




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
EV	70		0	RELEASE	4/16/96	SJM	LH
			A	REV PER 0B20-0491-97	5-6-97	DKE	MT
			B	REV PER 0B20-0798-98	7/23/98	DGG	KB

- 1

MATERIAL:
FRONT AND REAR SHELLS- STEEL.
HOUSING- UL 94V-0 RATED THERMOPLASTIC, BLACK.
OVERMOLD - PVC, COLOR: FROST WHITE.
- 2

FINISH:
FRONT AND REAR SHELLS - TIN PLATED.
3. LENGTHS LONGER THEN -1 EXCEED MAX LENGTH
a MAX CONDITIONS PER UNIVERSAL SERIAL BUS
SPEC. PARAGRAPH 6.4.



P1	WIRE COLOR	AWG
1	RED	24
2	WHITE	28
3	GREEN	28
4	BLACK	24
SHIELD	BRAID	36

3000 ⁺⁰ ₋₅₀	621747-4
500 ⁺⁰ ₋₂₅	621747-3
1500 ⁺⁰ ₋₅₀	621747-2
2000 ⁺⁰ ₋₅₀	621747-1
A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

MATERIAL

1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH 2

DWN S.J.MAGARO 4/16/96
CHK L.A.HUFF 4/26/96
APVD L.A.HUFF 4/26/96
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -
CUSTOMER DRAWING

NAME
CABLE ASSEMBLY, 4 POSN USB
PLUG, TYPE A, 28/24 AWG

SIZE A2
CAGE CODE 00779
DRAWING NO C=621747

SCALE 2:1
SHEET 1 OF 1
REV B

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

AMP 1471-9 REV 10/93

23-JUL-98 15:54:13 amp36728/home/amp36728/ednmod