

458139-1

1. APPLY PART NUMBER
PER PROCESS SPEC.
106-2 PARA. 3.3-A, B or C
IN AREA X




458139

2. DIMENSIONS I & II TO BE EQUAL WITHIN
.005

3. TOLERANCE APPLIES TO THIS SIDE ONLY.

4. DO NOT BREAK EDGES & CORNERS ON TOP
SIDE OF ANVIL, REMOVE BURRS ONLY.

5. APPLY PROTECTIVE COATING PER MES-107-1025



THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT
NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT
WRITTEN AUTHORIZATION FROM AMP REPRESENTATIVE, HARRISBURG, PA.

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

UNLESS OTHERWISE SPECIFIED		REMOVE BURRS, BREAK SHARP EDGES .015 R MAX		DECIMALS: .00 = .02, .000 = .003, .0000 = .0005		ANGLES: 30°		32J	
MATERIAL		100-43		DR 12-20-72		APP			
HEAT TREAT		111-43-5.3 R 56-58		DR 12-20-72		REL		12/23/72	
COATING OR PLATING		112-157		DR 12-20-72		REL		12/23/72	
PERMANENT FIRST USED		62129		MUNI APPL		A		458139-1	
TYPE		LW		NAME		ANVIL, SPECIAL			
LTR		REVISION RECORD		DATE		4-7			