


NUMBER
C-1775051







METRIC

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD. DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.


PRINT
DW

NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC HIGH TEMP., UL 94V-0 COLOR: GRAY.
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.25mm.
SHIELD: PHOSPHOR BRONZE, THICKNESS: 0.40mm.
- FINISH:
CONTACT: 30u" GOLD PLATING ON CONTACT AREA,
100u" MIN TIN-Cu PLATED ON SOLDER TAILS
50u" MIN NICKEL UNDERPLATED ALL OVER.
SHIELD: 100u" MIN HALF-BRIGH TIN PLATED OVER 80u" MIN Cu UNDERPLATED ALL OVER.
- REFLOW SOLDER CAPABLE TO 260°C PER TYCO SPEC 109-201, CONDITION C.
- RoHS 2002/95/EC COMPLIANT
- CHOOSE PRE-FIX FROM LEFT TABLE AND SUFFIX FROM RIGHT TABLE FOR DESIRED PART NUMBER COMBINATION.



RECOMMENDED PCB LAYOUT (MOUNTING SIDE)
(TOP VIEW) (TOLERANCE=±0.05)



0.10
ALL SOLDERTAILS & MOUNT PEGS

1775051-1

PART NUMBER

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3'		DWN O. HU 10-MAR-2005	TYCO HOLDINGS (BERMUDA) VII LTD. TAIWAN BRANCH	
MATERIAL SEE NOTE		CHK S. HOU 10-MAR-2005	NAME	
FINISH SEE NOTE		APVD W.J. KE 10-MAR-2005	MINI USB CONN., RCPT, 5 POS, SMT, AB TYPE	
		PRODUCT SPEC 108-57509	LOC DW	SIZE A ₃
		QUALIFICATION TEST REPORT 501-57637	DRAWING NO C-1775051	REV O
		WEIGHT 10.5 gram	SCALE --	SHEET 1 OF 2

O	FIRST RELEASED	FZ00-0042-05	OH SH	11MAR 2005
LTR	REVISION RECORD	ECN	DWN CHK	DATE




NUMBER
C-1775051

METRIC
3RD ANGLE PROJECTION






METRIC

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD. DIMENSION IN MILLIMETERS. DO NOT SCALE PRINT.

PRINT
DW



- NOTES :
- MATERIAL :
 - EMBOSSED CARRIER: PS
 - COVER TAPE: PET
 - SHIPPING CARTON: CORRUGATED FIBER.
 - DIMENSION :
 - REEL: W=24 , ϕ A=330
 - SHIPPING CARTON: L=349.2,W=147.6, H=156.
 - QUANTITY :
 - PRIMARY PACKING: 700PCS/REEL.
 - SECONDARY PACKING: 10REEL/ CARTON(7000PCS).
 - WEIGHT :
 - NET WEIGHT: 11.5kg/CARTON.
 - GROSS WEIGHT: 10.5kg/CARTON.
 - PEELING RESISTANCE: 10g~130g.
 - PELLING SPEED: 300mm/minutes.



TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN	O. HU	tyco TYCO HOLDINGS (BERMUDA) VII LTD. TAIWAN BRANCH
0 PLC	±		10-MAR-2005	
1 PLC	±	CHK	S. HOU	NAME
2 PLC	±		10-MAR-2005	
3 PLC	±			MINI USB CONN., RCPT, 5 POS, SMT, AB TYPE
ANGLES	±			
MATERIAL	-	APVD	W.J. KE	LOC SIZE DRAWING NO REV DW A ₃ C-1775051 O
		PRODUCT SPEC	10-MAR-2005	
FINISH	-	APPLICATION SPEC		SCALE SHEET -- 2 OF 2
		WEIGHT		

LTR	SEE SHEET 1.	ECN	DWN	DATE
	REVISION RECORD		CHK	