







Diode Modules

Type	Schematic Diagram	Part Number	Ratings and Characteristics								Outline Drawing
			Rated Voltage (V)	Rated Current (A)	Surge Current (A)	Junction Temp. (°C)	Insulation Voltage (V)	Forward Voltage (V) (1 min.)	Reverse Recovery Time (μs)	Thermal Resistance (°C/W)	
Rectifier Diode Module		6RI30E	600	30	360	150	2000	1.10	—	0.80	Fig. 1
		6RI50E		50	480			1.20	—	0.42	Fig. 3
		6RI75E		75	1000			1.15	—	0.30	Fig. 4
		6RI100E		100	1200			1.15	—	0.22	Fig. 4
		6RI30G	1200	30	320	150	2500	1.30	—	0.80	Fig. 2
		6RI75G		75	1000			1.30	—	0.30	Fig. 4
		6RI100G		100	1200			1.25	—	0.22	Fig. 4
		2RI60E	600	60X2	1200	150	2000	1.30	—	0.25	Fig. 5
		2RI100E	800	100X2	2000			1.30	—	0.20	Fig. 5
		2RI60G	1200	60X2	1200	150	2500	1.40	—	0.25	Fig. 5
		2RI100G	1600	100X2	2000			1.40	—	0.20	Fig. 5
		2RI150E	600	150X2	3200	150	2000	1.30	—	0.125	Fig. 6
		2RI250E	800	250X2	4500			1.30	—	0.10	Fig. 6
		ESAG01	100	50X2	1200	150	—	1.40	—	0.20	Fig. 10
		ESAH01		100X2	1500			1.35	—	0.20	Fig. 11
		ESAL01		150X2	2000			1.35	—	0.15	Fig. 11
Fast-Recovery Diode		ESAG73	300	50X2	800	150	—	1.50	0.5	0.30	Fig. 11
		ESAH73	600	100X2	1400			1.50		0.18	Fig. 11
		2FI50A	300	50X2	800	150	1500	1.25	0.5	0.40	Fig. 7
		2FI100A	600	100X2	1600			1.25		0.20	Fig. 7
		2FI200A	600	200X2	3200			1.25		0.20	Fig. 9
		2FI50F	300	50X2	800	150	1500	1.75	0.2	0.40	Fig. 8
		2FI100F	600	100X2	1600			1.75		0.22	Fig. 8
		2FI50G	1000	50X2	800	150	2000	1.65	0.6	0.40	Fig. 7
		2FI100G		100X2	1200			1.65		0.2	Fig. 7
		ERG28 ERG78	1200	30	500	125	—	3.0	0.5	0.8	Fig. 13
		1F60A		60	1000		—	3.0		0.32	Fig. 14
Schottky Barrier Diode		2BI60E	40	60X2	850	125	1500	0.58	—	0.35	Fig. 8
		2BI100E		100X2	1600			0.55	—	0.25	Fig. 8
		ESAG84		50X4	800		—	0.63	—	0.70	Fig. 12

DIMENSIONS IN MILLIMETERS

