


NOTES: 1. MATERIALS OF CONSTRUCTION: BODY, BARREL, HEX NUT, FERRULE - BRASS (ASTM-B16-H02, C36000), NICKEL PLATED (.000100 MIN) THICK CONTACT PIN - BRASS (ASTM-B16-H02, C36000), GOLD PLATED (.000003 MIN) THICK CONTACT PIN - PHOSPHOR BRONZE, GOLD PLATED (.000003 MIN) THICK INSULATORS (2) - PTFE, ASTM D 1710 OR EQUIV GASKET - SILICONE RUBBER, COLOR RED LOCK WASHER - BRASS, (QQ-B-613), NICKEL PLATED (.000100 MIN) THICK 2. CRIMP FERRULE HEX CRIMP SIZE .128 CONTACT PIN SQ. CRIMP SIZE .028 MAX PANEL THICKNESS = 6,5mm [.256]	82-6093-RFX		REVISIONS			
	DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
	THIRD ANGLE PROJ. 	A	RELEASE TO MFG.	10/7/99	43148	CPM
		B	ADD NOTE 2	3/8/00	43268	CPM
		C	SEE SHEET 1	4/12/05	45499	CPM



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°	MATERIAL	DRAWN C. McGRATH	DATE 25-Sep-99	TITLE N BULKHEAD CRIMP JACK (FOR RG-174/U, 188A/U, 316/U)		Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com	
		ENGINEER T. AUBIN	DATE 25-Sep-99				
		APPROVED T. AUBIN	DATE 10/6/99				
		CAD FILE I:\N\82-6093-RFX	CODE ID 74868	DWG SIZE B	DRAWING NO. 82-6093-RFX	REV C	SCALE: 3.0:1 SHEET 2 OF 2