


REV.	DATE	DESCRIPTION
NC	04/25/06	INITIAL RELEASE



NOTE:
1. CRIMPED FERRULE – HEX CRIMP SIZE .429"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex									
7						DRAWN	G.R.S.					04/25/06					
6						CHECKED											
5	COVER	BRASS	NICKEL	1			ISSUED		PART DESCRIPTION								
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1		TNC REVERSE POLARITY R/A CRIMP PLUG (FOR RG-8/U, 213/U, LMR400, BELDEN 9913,9914)								
3	CONTACT PIN	PHOS. BRONZE	GOLD	1		PART NO.											
2	INSULATOR	TEFLON	NATURAL	1		122416RP											
1	BODY	BRASS	NICKEL	1		CAD FILE			DWG. NO.		122416RP.DWG	REV.	NC	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	C:/122/122416RP.DWG											