

S53 SERIES MATRIX

S 5 3 2 X X X X X X X X X

SERIES
S53- INTERNAL
THREAD
FORM A

POLES
2- 2 POLE

THREAD
09- PG9
11- PG11
M6-M6x1.5

MATERIAL AND
HOUSING COLOR:
G - PA6 Grey
N - Black Black
T - Transparent
W- Black
UL94- V0


CIRCUIT
SEE DETAILS
IN CATALOGUE

VOLTAGE
SEE DETAILS
IN CATALOGUE

SCREW AND GASKET
1- NBR PROFILE GASKET & SCREW
2- NBR FLAT GASKET & SCREW
T- NBR PROFILE GASKET & IP67 SCREW



NON STANDARD COMPONENTS
AF- WITH CENTRE SCREW MOUNTED
14- SINGLE BAGGED
SA- UL LISTED
AN-CIRCUIT R0 WITH 3 DIODES x
ELECTRIX (1002-97)

SEE TABLE 1 FOR GASKET AND SCREW TYPES



ITEM NO	DESCRIPTION
1	COVER + INSERT ASSEMBLY
2	GASKET
3	SCREW

EARTH POSITION
H12 SHOWN



TECHNICAL SPECIFICATION:

OPERATING CURRENT: 16A
CONTACT RESISTANCE: <15 mOhms MAX.

OPERATING TEMPERATURE:
NBR GASKET: -40° TO +90°C
SILICONE GASKET: -40° TO 125°C

TABLE 1

PROFIED GASKET	FLAT GASKET	SCREW M3x36
		SCREW M3x36 + WASHER

DOCUMENT STATUS	P1	RELEASE DATE	2019/05/30	09:43:21
-----------------	----	--------------	------------	----------

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
 = 0	DIMENSION UNITS	SCALE	CURRENT REV DESC:		
	mm	2:1			
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				
 = 0	ANGULAR TOL ± 1.0 °				
 = 0	4 PLACES ±				
 = 0	3 PLACES ±		EC NO: 618236		
 = 0	2 PLACES ± 0.05		DRWN: MCELEJEWSKI 2019/05/30		
 = 0	1 PLACE ± 0.3		CHK'D: DSTACHOWIAK 2019/05/30		
 = 0	0 PLACES ± 0.5		APPR: DSTACHOWIAK 2019/05/30		
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		INITIAL REVISION:		
			DRWN: MDHARMANTI 2018/11/23		
			APPR: RSILLER 2019/02/01		
			THIRD ANGLE PROJECTION		
			DRAWING		
			SERIES		
			A3-SIZE		
			121064		
			MATERIAL NUMBER		
			CUSTOMER		
			SHEET NUMBER		
			PART LIST		
			GENERAL MARKET		
			1 OF 2		

PART LIST

ENGINEERING NO.	MOLEX PN	EARTH
S53209NR021	1210640896	H12
S53209GR051	1210640891	H12
S53209NE151	1210640894	H12
S53209NR031	1210640898	H12
S53209NR041	1210640899	H12
S53209NR051	1210640900	H12
S53209NR051AF	1210650593	H12
S53209NR052	1210640901	H12
S53209TC321	1210640918	H12
S53209TC411	1210640923	H12
S53209TC421	1210640924	H12
S53209TC441	1210640926	H12
S53209TC451	1210640927	H12
S53209TC4B1	1210640928	H12
S53209TC4D1	1210640930	H12
S53209TC4E1	1210640932	H12
S53209TC4H1	1210640934	H12
S53209TC4L1	1210640936	H12
S53209TC4M1	1210640937	H12
S53209TG221	1210640939	H12
S53209TR211	1210640944	H12
S53209TR221	1210640945	H12
S53209TR241	1210640948	H12
S53209TR251	1210640949	H12
S53209TR252	1210640950	H12
S53209TR2H1	1210640953	H12
S53209TR2L1	1210640954	H12
S53209TR2M1	1210640955	H12
S53209TU021	1210640964	H12
S53211GR031	1210640971	H12
S53211GR041	1210640972	H12
S53211GR051	1210640973	H12
S53211NR021	1210640975	H12
S53211NR031	1210640977	H12
S53211NR041	1210640978	H12
S53211NR051	1210640979	H12
S53211NR052	1210640980	H12
S53211TC321	1210640996	H12
S53211TC421	1210641001	H12
S53211TC421AF	1210641705	H12

ENGINEERING NO.	MOLEX P/N	EARTH
S53211TC441	1210641003	H12
S53211TC451	1210641004	H12
S53211TC4B1	1210641005	H12
S53211TC4H1	1210641007	H12
S53211TR221	1210641014	H12
S53211TR241	1210641016	H12
S53211TR251	1210641017	H12
S532M6NR021	1210641698	H12
S532M6NR051	1210641542	H12
S532M6TC421	1210641422	H12
S532M6TS021	1210641452	H12
S53209NE051	1210640893	H12
S53209NR0612110*	1210650520*	H12
S53209NR061	1210641425	H12
S53209NR061AN	1210650521	H12
S53209TR221AF	1210641734	H12
S532M6TC321	1210641788	H12
S53211WE151SA	1210641813	H12
S53211TA1L10458*	1210641681*	H12
S53209NR05T14	1210641798	H12
S53209NR02T14	1210641816	H12
A1 S53209WR041SA	1210641589	H12

NOTE:
* P/N 1210650521 & 1210641681 are special customer P/N's.

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex		
	mm		2:1									
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 618236 DRWN: MCELEJEWSKI 2019/05/30 CHK'D: DSTACHOWIAK 2019/05/30 APPR: DSTACHOWIAK 2019/05/30 INITIAL REVISION: DRWN: MDHARMANTI 2018/11/23 APPR: RSILLER 2019/02/01					PRODUCT CUSTOMER DRAWING				
	ANGULAR TOL ± 1.0 °											
	4 PLACES ±											
	3 PLACES ±											
	2 PLACES ± 0.05											
	1 PLACE ± 0.3		DOCUMENT NUMBER					DOC TYPE	DOC PART	REVISION		
	0 PLACES ± 0.5											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
				A3-SIZE	121064	PART LIST		GENERAL MARKET		2 OF 2		