






PLF-15DZB2

PART NUMBER	RATED VOLTAGE	RATED CURRENT	GROUND CAPACITANCE	LEAKAGE CURRENT
PLF-3DZB21	250V AC	3 AMP	4.7 nF	0.5mA MAX.
PLF-6DZB21	250V AC	6 AMP	4.7 nF	0.5mA MAX.
PLF-10DZB21	250V AC	10 AMP	3.3 nF	0.5mA MAX.
PLF-15DZB2	250V AC	15 AMP	3.3 nF	0.5mA MAX.



Insertion Loss in dB (Measured in 50Ω systems, as IEC / cispr No.

