

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

BELDEN
SENDING ALL THE RIGHT SIGNALS

38208 Hook-up/Lead - UL Type PV Wire



For more Information
please call

1-800-Belden1



Description:

8 AWG stranded (133x29) tinned copper conductors, XLPE insulation, non-integrally PVC jacketed, sunlight resistant, photovoltaic wire.

Usage (Overall)

Suitable Applications:	Interconnection wiring of grounded and ungrounded photovoltaic power systems as described in Section 690.31(A) of the 2008 NEC.
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	8	133x29	TC - Tinned Copper

Total Number of Conductors:	1
-----------------------------	---

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
XLPE - Cross Linked Polyethylene	0.063

Separator

Separator Material over Conductor:	Y
------------------------------------	---

Jacket

Jacket Material:	PVC - Polyvinyl Chloride
------------------	--------------------------

Jacket Thickness:	.033
-------------------	------

Overall Cable

Overall Nominal Diameter:	0.364 in.
---------------------------	-----------

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +90°C
------------------------------	----------------

UL Temperature Rating:	90°C Wet/Dry
------------------------	--------------

Bulk Cable Weight:	98 lbs/1000 ft.
--------------------	-----------------

Max. Recommended Pulling Tension:	213 lbs.
-----------------------------------	----------

Min. Bend Radius/Minor Axis:	3.625 in.
------------------------------	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	600V, 90C
------------	-----------

UL Type:	PV, USE-2, RHW-2
----------	------------------

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	09/01/2009
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

38208 Hook-up/Lead - UL Type PV Wire

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: VW-1

Suitability

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
0.610

Max. Operating Voltage - UL:

Voltage
600 V RMs

Max. Recommended Current:

Description	Current
Single conductor in free air @ 30 ambient	80 amps

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
38208 0101000	1,000 FT	107.000 LB	BLACK	C	#8 XLPE PVC
38208 0105000	5,000 FT	540.000 LB	BLACK	C	#8 XLPE PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 09-24-2010

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[38208 0101000](#) [38208 0105000](#)