

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [75705-0604](#)
Status: **Active**
Overview: GbX I-Trac™ Backplane Connector System
Description: 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 6 Columns, 132 Circuits, Mating Pin Length 5.70mm
Replacement Part Number: 757051604

Documents:
[3D Model](#) [Product Specification PS-75710-999 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [75705](#)
Application Backplane, Midplane, Orthogonal
Component Type PCB Header
Overview [GbX I-Trac™ Backplane Connector System](#)
Product Name GbX I-Trac™
Replacement Part Number 757051604
Style N/A
UPC 822350333641

Physical

Circuits (Loaded) 132
Circuits (maximum) 132
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin-Lead
Material - Resin High Temperature Thermoplastic
Net Weight 4.050/g
Number of Columns 6
Number of Pairs 6, Open Pin Field
Number of Rows 11
Orientation Vertical
PC Tail Length 2.10mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.85mm, 3.70mm
Pitch - Termination Interface 1.00mm, 2.70mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to PCB No
Stackable Yes
Surface Mount Compatible (SMC) Yes




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[75705Series](#)

Mates With

[75710](#) GbX I-Trac™ Right Angle Receptacle
Module

Use With

[78232](#) GbX I-Trac™ Vertical Power
Receptacle. [75234](#) Backplane Free Standing
Guide Pin

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Backplane Header	0621009610
Removal Tool for GbX-U™, I-Trac™, Impact™, or TinMan	

Temperature Range - Operating	-55°C to +80°C	Backplane Insertion	<u>0621005110</u>
Termination Interface: Style	Through Hole - Compliant Pin	Tool for Signal	Contact Insertion
Electrical		Press-In Tool for	<u>0622018602</u>
Current - Maximum per Contact	1A	Vertical Header 11-	Row, 6-Column
Data Rate	12.0 Gbps		
Real Signals (per 25mm)	148		
Shield Type	N/A		
Shielded	No		
Voltage - Maximum	120V AC (RMS)/DC		
Material Info			
Reference - Drawing Numbers			
Product Specification	PS-75710-999		
Sales Drawing	SD-75705-001		

This document was generated on 03/13/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75705-0604](#)