

HBL5392-- Straight Blade Products, Combination Duplex



2-Pole 3Wire Grounding, 20A 125V^{250V}R, Nylon Face, Back and Side Wired, Brown (20A Only)

HBL5292

Product Specifications

Product Type	 Combo Face Duplexes
Hospital Grade ?	No
Receptacle Grade	Heavy Duty Spec Grade
Face Style	Finder Groove
Face A	5-20A
Face B	5-20A
Color	 Brown
NEMA No.	5-20R Only
Horsepower	1
Type	2 Pole, 3 Wire, Grounding
Rating	20A, 125V
Certification	-UL Listed to UL498 File E2186, Guide RTRT Fed Spec WC596G, Meets 15A Duty and W requirements, Certified to CSA, C22.2, No. 42 file 285.
Terminal Screw Material	#8-32 Brass, Multiple Drive
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Top Material	Nylon
Base Material	Reinforced PET
Power Contacts Material	.037" (.9) Brass
Mounting Strap Material	.050" (1.3) Brass
Auto Ground Clip Material	Stainless Steel
Mounting Screw Material	SteelZinc Plated
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#14#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	Top: UL 94 V2. Base: UL 94 V0 and UL594A.
Operating Temperatures	Maximum continuous 75°C, minimum 40°C (w/o impact).
MDrawings	Click here for MDrawing
Catalog Page	Click here for catalog page A43
Catalog Section	Click here for Section
UPC Number	783585014746
Weight in LBs	0.250