


AD9225GP SERIES




External Dimensions



Frame: Plastic (UL: 94V-0)
Impeller: Plastic (UL: 94V-0)
Lead wire: UL 1007 AWG24


Specifications(Nominal)

*: Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	*Noise Level (dB/A)	Weight (g)
92x92x25	AD0912HB-A7BGP	◎	12	0.19	2.28	3000	1.530	54.172	0.174	4.420	41.0	103.0
	AD0912UB-A7BGP	◎	12	0.37	4.44	3500	1.790	63.397	0.237	6.020	45.7	
	AD0912XB-A7BGP	◎	12	0.47	5.64	4000	2.110	74.515	0.313	7.950	50.2	
	AD0924HB-A7BGP	◎	24	0.12	2.88	3000	1.530	54.172	0.174	4.420	41.0	
	AD0924UB-A7BGP	◎	24	0.18	4.32	3500	1.790	63.397	0.237	6.020	45.7	
	AD0924XB-A7BGP	◎	24	0.24	5.76	4000	2.110	74.515	0.313	7.950	50.2	
	AD0948HB-A7BGP	◎	48	0.08	3.84	3000	1.530	54.172	0.174	4.420	41.0	
	AD0948UB-A7BGP	◎	48	0.12	5.76	3500	1.790	63.297	0.237	6.020	45.7	
	AD0948XB-A7BGP	◎	48	0.17	8.16	4000	2.110	74.515	0.313	7.950	50.2	

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓					✓		✓

*Safety approvals

				✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0912UB-A73GL-LF](#)