

MC9S08SH16VTJ Information

- General information
- Package information
- Environmental and Compliance information
- Manufacturing and Qualification information
- Ordering information
- Operating Characteristics

General Information

Parameter	Value
Part Number	MC9S08SH16VTJ
Description	S08 16K FLASH
Product Line	G9TZSH32
PTI	JDTS
Material Type	Tested Packaged Device
Life Cycle Description (code)	PRODUCT NEWLY INTRO D/RAMPUP(1)
Status	Active

Package Information

Parameter	Value
Package Description	TSSOP 20 4.4*6.5*1.P.65
JEDEC Pkg Description	TS-PDSO-G20
Pin/Lead/Ball Count	20
Package Material	Plastic
Mounting Style	Surface Mount
Tape & Reel	No

Environmental and Compliance Information

Parameter	Value
Pb-Free	
RoHS Compliant	
Halogen Free	Yes
Product Content Report	Product Content Report
RoHS CoA	Contact Us
2nd Level Interconnect	e3
Moisture Sensitivity Level (MSL)	3
Floor Life	168 HOURS
Package Peak Temperature (°C)	260

Manufacturing and Qualification information

Parameter	Value
Micron Size (μm)	.25
Application/Qualification Tier	COMMERCIAL, INDUSTRIAL, AUTOMOTIVE

Ordering Information

Parameter	Value
Minimum Package Quantity (MPQ)	75
MPQ Container	RAIL
Preferred Order Quantity (POQ)	2250
POQ Container	BOX
Export Control Classification Number (US)	EAR99
Harmonized Tariff (US)disclaimer	8542.31.0000
Budgetary Price QTY 1000+ (\$US)	-

Operating Characteristics

Parameter	Value
Bus Frequency (Max) (MHz)	20
Core - Number of Cores (Spec)	1
Core - Operating Frequency (Max) (MHz)	40
Core - Type	HCS08