

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0874370543

Status:


Active - Custom

Overview:

Pico-Spox™

Description:

1.50mm (.059") Pitch Pico-SPOX™ Wire-to-Board Header, Surface Mount, Vertical, Shrouded, 5 Circuits, Embossed Tape on Reel Packaging, Lead-free



Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Literature \(PDF\)](#)

[Product Specification PS-87437 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	PCB Headers
Series	87437
Application	Wire-to-Board
Overview	Pico-Spox™
Product Literature Order No	USA-235
Product Name	Pico-SPOX™
Physical	
Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface (in)	0.059 In
Pitch - Mating Interface (mm)	1.50 mm
Plating min: Mating (µin)	100
Plating min: Mating (µm)	2.50
Plating min: Termination (µin)	100
Plating min: Termination (µm)	2.50
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum	1.5A, 2A, 3A
Voltage - Maximum	350V
Material Info	
Reference - Drawing Numbers	

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87437Series

Mates With

87439 Pico-SPOX™ Wire-to-Board Housing.

87421 Pico-SPOX™ Crimp Terminal

Product Specification

Sales Drawing

PS-87437, RPS-87437, RPS-87437-001,
RPS-87437-200
SD-87437-**31

This document was generated on 02/04/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION