





SHEET OF



RECOMMEND P.C.B. LAYOUT



CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-1	OPEN	2-3

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: 0.0±0.4
0.00±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 5A @120VAC or 28VDC; 2A @250VAC
- FIXED TERMINAL & MOVING CONTACT: Silver plated copper alloy.
- CONTACT RESISTANCE: 10m ohm typical.
- ELECTRICAL LIFE: 30,000 Actuations at full load.
- INSULATION RESISTANCE: 1,000 M ohm min.
- DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
- OPERATING TEMP.: -30°C to 85°C.

C	21566	DIM 6.60 WAS 6.35	9/03/14	rc
B	11849	DIM 7.24 WAS 7.62	12/07/01	RSB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE

500 SSP-1 S2 M2 Q E A

SCALE

2:1

DATE

2/16/00

DR

MM

DWG

T511028

REV

C