

MOS FET Relays G3VM-41LR10

SSOP Package MOS FET Relays with Low Leakage Current, Output Capacitance and ON Resistance ($C \times R = 5.4 \text{ pF} \cdot \Omega$) in a 40-V Load Voltage Model.

- Output capacitance of 0.45 pF (typical) allows high frequency applications.
- Leakage current of 0.2 nA max. (10 pA typ.) when relay is open
- Turn-on time = 0.026 ms (typ.)
- RoHS compliant

■ Application Examples

- Semiconductor inspection tools
- Measurement devices and Data loggers
- Broadband systems



NEW

Note: The actual product is marked differently from the image shown here.




■ List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per tape
SPST-NO	Surface-mounting terminals	40 VAC	G3VM-41LR10	---
			G3VM-41LR10(TR05)	500
			G3VM-41LR10(TR)	1,500

■ Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-41LR10




Note: The actual product is marked differently from the image shown here.

Note: A tolerance of $\pm 0.1 \text{ mm}$ applies to all dimensions unless otherwise specified.

Weight: 0.03 g


■ Terminal Arrangement/Internal Connections (Top View)

G3VM-41LR10



■ Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-41LR10



■ Absolute Maximum Ratings (Ta = 25°C)


Item		Symbol	Rating	Unit	Measurement Conditions
Input	LED forward current	I _F	30	mA	
	LED forward current reduction rate	Δ I _F /°C	−0.3	mA/°C	T _a ≥ 25°C
	LED reverse voltage	V _R	5	V	
	Connection temperature	T _j	125	°C	
Output	Load voltage (AC peak/DC)	V _{OFF}	40	V	
	Continuous load current	I _O	120	mA	
	ON current reduction rate	Δ I _{ON} /°C	−1.2	mA/°C	T _a ≥ 25°C
	Connection temperature	T _j	125	°C	
Dielectric strength between input and output (See note 1.)		V _{I-O}	1,500	V _{rms}	AC for 1 min
Ambient operating temperature		T _a	−20 to +85	°C	With no icing or condensation
Storage temperature		T _{stg}	−40 to +125	°C	With no icing or condensation
Soldering temperature		---	260	°C	10 s

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics (Ta = 25°C)

Item		Symbol	Mini- mum	Typical	Maxi- mum	Unit	Measurement conditions
Input	LED forward voltage	V _F	1.15	1.35	1.45	V	I _F = 5 mA
	Reverse current	I _R	---	---	10	μA	V _R = 5 V
	Capacity between terminals	C _T	---	70	---	pF	V = 0, f = 1 MHz
	Trigger LED forward current	I _{FT}	---	---	3	mA	I _O = 100 mA
Output	Maximum resistance with output ON	R _{ON}	---	12	14	Ω	I _F = 5 mA, I _O = 120 mA, t < 1 s
	Current leakage when the relay is open	I _{LEAK}	---	10	200	pA	V _{OFF} = 35 V, T _a = 25°C
	Capacity between terminals	C _{OFF}	---	0.45	0.8	pF	V = 0, f = 100 MHz, t = < 1 s
Capacity between I/O terminals		C _{I-O}	---	0.3	---	pF	f = 1 MHz, V _s = 0 V
Insulation resistance between I/O terminals		R _{I-O}	1,000	---	---	MΩ	V _{I-O} = 500 VDC, R _{OH} ≤ 60%
Turn-ON time		t _{ON}	---	0.026	0.2	ms	I _F = 5 mA, R _L = 200 Ω, V _{DD} = 10 V (See note 2.)
Turn-OFF time		t _{OFF}	---	0.14	0.3	ms	

Note: 2. Turn-ON and Turn-OFF Times



■ Recommended Operating Conditions


Use the G3VM under the following conditions so that the Relay will operate properly.

Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	32	V
Operating LED forward current	I_F	---	---	20	mA
Continuous load current (AC peak/DC)	I_O	---	---	120	mA
Operating temperature	T_a	25	---	60	°C

Engineering Data


LED forward current vs.
Ambient temperature

$I_F - T_a$




Continuous load current vs.
Ambient temperature

$I_O - T_a$




LED forward current vs.
LED forward voltage

$I_F - V_F$




Continuous load current vs.
On-state voltage

$I_O - V_{ON}$




On-state resistance vs.
Ambient temperature

$R_{ON} - T_a$




Trigger LED forward current vs.
Ambient temperature

$I_{FT} - T_a$




Turn ON, Turn OFF time vs.
LED forward current

$t_{ON}, t_{OFF} - I_F$




Turn ON, Turn OFF time vs.
Ambient temperature

$t_{ON}, t_{OFF} - T_a$



Current leakage vs.
Ambient temperature

$I_{LEAK} - T_a$



onlinecomponents.com

All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X302-E-1

12/10

Specifications subject to change without notice

Printed in USA