


## Specifications




|                                                         |                     |                  |                          |
|---------------------------------------------------------|---------------------|------------------|--------------------------|
| Type : Nickel-Metal Hydride Battery                     |                     |                  | Size : AAA Consumer Type |
| Capacity ㉑                                              | Typical             |                  | 800mAh                   |
|                                                         | Minimum             |                  | 740mAh                   |
| Nominal Voltage                                         |                     |                  | 1.2V                     |
| Charging Current × Time                                 |                     | Fast Charge ㉓    | 800 mA × about 1.1h      |
| Ambient Temp.                                           | Charge Condition    | Fast Charge ㉓    | 0°C - 40°C               |
|                                                         | Discharge Condition |                  | 0°C - 50°C               |
|                                                         | Storage Condition   | Less than 30days | -20°C - 50°C             |
|                                                         |                     | Less than 90days | -20°C - 40°C             |
|                                                         |                     | Less than 1year  | -20°C - 30°C             |
| Internal Impedance ㉔<br>(after discharge to E.V. =1.0V) |                     |                  | Approx. 40mΩ(at 1000Hz)  |
| Weight ㉕                                                |                     |                  | Approx. 13 g             |
| Size ㉖ : (Diameter) × (Height)                          |                     |                  | 10.5(D) × 44.0(H) mm     |

- 1)Single cell capacity under the following condition.  
Charge : 80mA×16h, Discharge : 160mA(E.V.=1.0V) at 20°C
- 2)Use recommended charging system.
- 3)After a few charge and discharge cycles under the above 1) condition.
- 4)With tube.

## Typical Characteristics

### Charge



### Discharge

