

FRED

**HFB60HF20C**

Ultrafast, Soft Recovery Diode

**Features**

- Reduced RFI and EMI
- Reduced Snubbing
- Extensive Characterization of Recovery Parameters
- Hermetic
- Surface Mount

$$V_R = 200V$$

$$I_{F(AV)} = 60A$$

$$t_{rr} = 35ns$$

**Description**



These Ultrafast, soft recovery diodes are optimized to reduce losses and EMI/RFI in high frequency power conditioning systems. An extensive characterization of the recovery behavior for different values of current, temperature and di/dt simplifies the calculations of losses in the operating conditions. The softness of the recovery eliminates the need for a snubber in most applications. These devices are ideally suited for power converters, motors drives and other applications where switching losses are significant portion of the total losses.

**Absolute Maximum Ratings**

|                          | Parameter                                                      | Max.        | Units      |
|--------------------------|----------------------------------------------------------------|-------------|------------|
| $V_R$                    | Cathode to Anode Voltage ( Per Leg )                           | 200         | V          |
| $I_{F(AV)}$              | Continuous Forward Current, ① $T_C = 50^\circ C$               | 60          | A          |
| $I_{FSM}$                | Single Pulse Forward Current, ② $T_C = 25^\circ C$ ( Per Leg ) | 300         |            |
| $P_D @ T_C = 25^\circ C$ | Maximum Power Dissipation                                      | 46          | W          |
| $T_J, T_{STG}$           | Operating Junction and Storage Temperature Range               | -55 to +150 | $^\circ C$ |

**Note:** ① D.C. = 50% rect. wave

② 1/2 sine wave, 60 Hz , P.W. = 8.33 ms



**Electrical Characteristics ( Per Leg ) @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**


|          | Parameter                             | Min. | Typ. | Max. | Units         | Test Conditions                                            |
|----------|---------------------------------------|------|------|------|---------------|------------------------------------------------------------|
| $V_{BR}$ | Cathode Anode Breakdown Voltage       | 200  | —    | —    | V             | $I_R = 100\mu\text{A}$                                     |
| $V_F$    | Forward Voltage<br>See Fig. 1         | —    | —    | 1.19 | V             | $I_F = 30\text{A}, T_J = -55^\circ\text{C}$                |
|          |                                       | —    | —    | 1.08 |               | $I_F = 30\text{A}, T_J = 25^\circ\text{C}$                 |
|          |                                       | —    | —    | 1.25 |               | $I_F = 60\text{A}, T_J = 25^\circ\text{C}$                 |
|          |                                       | —    | —    | 1.22 |               | $I_F = 60\text{A}, T_J = 125^\circ\text{C}$                |
| $I_R$    | Reverse Leakage Current<br>See Fig. 2 | —    | —    | 10   | $\mu\text{A}$ | $V_R = V_R \text{ Rated}$                                  |
|          |                                       | —    | —    | 100  | $\mu\text{A}$ | $V_R = V_R \text{ Rated}, T_J = 125^\circ\text{C}$         |
| $C_T$    | Junction Capacitance, See Fig. 3      | —    | —    | 140  | pF            | $V_R = 200\text{V}$                                        |
| $L_S$    | Series Inductance                     | —    | 5.9  | —    | nH            | Measured from center of cathode pad to center of anode pad |

**Dynamic Recovery Characteristics ( Per Leg ) @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**


|                   | Parameter                             | Min. | Typ. | Max. | Units                  | Test Conditions                                                        |
|-------------------|---------------------------------------|------|------|------|------------------------|------------------------------------------------------------------------|
| $t_{rr}$          | Reverse Recovery Time                 | —    | —    | 35   | ns                     | $I_F = 1.0\text{A}, V_R = 30\text{V}, di/dt = 200\text{A}/\mu\text{s}$ |
| $t_{rr1}$         | Reverse Recovery Time                 | —    | 35   | —    | ns                     | $T_J = 25^\circ\text{C}$ See Fig. 5                                    |
| $t_{rr2}$         |                                       | —    | 58   | —    |                        | $T_J = 125^\circ\text{C}$ See Fig. 6                                   |
| $I_{RRM1}$        | Peak Recovery Current                 | —    | 3.8  | —    | A                      | $T_J = 25^\circ\text{C}$ See Fig. 7                                    |
| $I_{RRM2}$        |                                       | —    | 8.0  | —    |                        | $T_J = 125^\circ\text{C}$ See Fig. 8                                   |
| $Q_{rr1}$         | Reverse Recovery Charge               | —    | 77   | —    | nC                     | $T_J = 25^\circ\text{C}$ See Fig. 7                                    |
| $Q_{rr2}$         |                                       | —    | 240  | —    |                        | $T_J = 125^\circ\text{C}$ See Fig. 8                                   |
| $di_{(rec)M}/dt1$ | Peak Rate of Fall of Recovery Current | —    | 470  | —    | $\text{A}/\mu\text{s}$ | $T_J = 25^\circ\text{C}$ See Fig. 8                                    |
| $di_{(rec)M}/dt2$ | During $t_b$                          | —    | 640  | —    |                        | $T_J = 125^\circ\text{C}$ See Fig. 8                                   |

**Thermal - Mechanical Characteristics**


|            | Parameter                               | Typ. | Max. | Units                     |
|------------|-----------------------------------------|------|------|---------------------------|
| $R_{thJC}$ | Junction-to-Case, Single Leg Conducting | —    | 2.73 | $^\circ\text{C}/\text{W}$ |
| Wt         | Weight                                  | 2.6  | —    | g                         |




**Fig. 1** - Maximum Forward Voltage Drop Vs. Instantaneous Forward Current ( Per Leg )







**Fig. 2** - Typical Reverse Current Vs. Reverse Voltage ( Per Leg )




**Fig. 3** - Typical Junction Capacitance Vs. Reverse Voltage ( Per Leg )



**Fig. 4** - Maximum Thermal Impedance  $Z_{thjc}$  Characteristics ( Per Leg )

Fig. 5 - Typical Reverse Recovery Vs.  $di_f/dt$  ( Per Leg )Fig. 6 - Typical Recovery Current Vs.  $di_f/dt$  ( Per Leg )Fig. 7 - Typical Stored Charge Vs.  $di_f/dt$  ( Per Leg )Fig. 8 - Typical  $di_{(rec)M}/dt$  Vs.  $di_f/dt$  ( Per Leg )



**Fig. 10 - Reverse Recovery Waveform and Definitions**

Technical drawing of a mechanical part, showing three views: front, side, and top. The drawing includes dimensions in millimeters (mm) and inches (in), surface texture symbols, and feature callouts.

**Front View Dimensions:**

- Overall width: 11.55 [ .455 ]
- Overall height: 16.00 [ .630 ] / 15.75 [ .620 ]
- Top flange width: 11.31 [ .445 ]
- Top flange thickness: 3x 0.508 [ .020 ] / 0.254 [ .010 ]

**Side View Dimensions:**

- Overall width: 3.58 [ .141 ] MAX.
- Overall height: 8.61 [ .339 ]
- Bottom flange thickness: 1.99 [ .0785 ]
- Bottom flange width: 2x 3.68 [ .145 ] / 3.43 [ .135 ]

**Top View Dimensions:**

- Overall width: 9.65 [ .380 ] / 9.40 [ .370 ]
- Overall height: 10.66 [ .420 ] / 10.42 [ .410 ]
- Top flange width: 0.76 [ .030 ] MIN.
- Top flange thickness: 4.11 [ .162 ] / 3.87 [ .152 ]
- Top flange width: 0.89 [ .035 ] MIN.
- Top flange thickness: 2.67 [ .105 ]
- Top flange width: 5.33 [ .210 ]

**Surface Texture Symbols:**

- Symbol 1:  $\Delta 0.102 [ .004 ]$  3 SURFACES
- Symbol 2:  $\Delta 0.102 [ .004 ]$  3 SURFACES
- Symbol 3:  $\Delta 0.102 [ .004 ]$  3 SURFACES
- Symbol 4:  $\Delta 0.102 [ .004 ]$  3 SURFACES
- Symbol 5:  $\Delta 0.102 [ .004 ]$  3 SURFACES

**Feature Callouts:**

- Feature 1:  $\Phi 0.254 [ .010 ] \text{ @ } C A$
- Feature 2:  $\Phi 0.254 [ .010 ] \text{ @ } C A$
- Feature 3:  $\Phi 0.254 [ .010 ] \text{ @ } C A$
- Feature 4:  $\Phi 0.254 [ .010 ] \text{ @ } C A$
- Feature 5:  $\Phi 0.254 [ .010 ] \text{ @ } C A$

1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
4. DIMENSION INCLUDES METALLIZATION FLASH.
5. DIMENSION DOES NOT INCLUDE METALLIZATION FLASH.

1 = COMMON CATHODE  
2 = ANODE 1  
3 = ANODE 2

International  
**IOR** Rectifier

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.  
Data and specifications subject to change without notice. 07/01