



SRJ-SERIES



Suggested PCB Layout




Position Options




8 Position 10 Position 16 Position
(PCB Layout Differs)

Actuator Options




Extended Flush

SRK-SERIES



Suggested PCB Layout




Position Options



10 Position 16 Position

Actuator Options



Extended Flush

FEATURES:

- 3x2, 3x3, and 4x1 Pin Layouts
- Through Hole and Surface Mount Versions
- Washable
- Superior Quality


SPECIFICATIONS:

RATING: 100mA 5VDC (Switching)
100mA 50VDC (Non-Switching)
TEMPERATURE: -10°C to 60°C (Operating)
-40°C to 85°C (Storage)
OPERATING FORCE: 400gf·cm
ELECTRICAL LIFE: 15,000 Cycles
CONTACT RESISTANCE: 100mΩ Max.
INSULATION RESISTANCE: 100MΩ at 250VDC
DIELECTRIC STRENGTH: 250VAC for 1 Minute


MATERIALS:

BASE: Polyphenylene Sulfide (PPS)
HOUSING: Polyphenylene Sulfide (PPS)
ACTUATOR: Polyacetal
O-RING: NBR
CONTACT: Glass Fabric Epoxy Resin
Gold Over Nickel Plated
TERMINALS: Gold Over Nickel Plated Bronze
Tin Over Nickel Plated Bronze

SRM-SERIES



Suggested PCB Layout




Position Options




10 Position 16 Position

SRT-SERIES



Suggested PCB Layout





Position Options



10 Position 16 Position

Right Angle Option



SRJ-8
SRJ-10HC



SRT-10

EXAMPLE PART NUMBERS:

SRJ-10	10 Position
2x3, Through Hole, Flush, Real Code	
SRJ-16	16 Position
2x3, Through Hole, Flush, Real Code	
SRK-10	10 Position
3x3, Through Hole, Flush, Real Code	
SRK-10C	10 Position
3x3, Through Hole, Flush, Comp. Code	
SRK-10H	10 Position
3x3, Through Hole, Raised, Real Code	
SRK-16	16 Position
3x3, Through Hole, Flush, Real Code	
SRK-16C	16 Position
3x3, Through Hole, Flush, Comp. Code	
SRK-16H	16 Position
3x3, Through Hole, Raised, Real Code	
SRK-16HC	16 Position
3x3, Through Hole, Raised, Comp. Code	
SRM-10	10 Position
3x3, SMT, Flush Actuator, Real Code	
SRM-10C	10 Position
3x3, SMT, Flush Actuator, Comp. Code	
SRM-16	16 Position
3x3, SMT, Flush Actuator, Real Code	
SRM-16C	16 Position
3x3, SMT, Flush Actuator, Comp. Code	
SRT-10	10 Position
4x1, Through Hole, Flush, Real Code	

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

Series	Number of Positions	Actuator Options	Right Angle Option	Encoding Options	Tape Sealing	Packaging Options
SRJ - 2x3, Through Hole	8	For SRJ and SRK Series:	For SRJ, SRK, and SRM Series:	None - Real	For SRJ, SRK, and SRT Series:	For SRJ, SRK, and SRT Series:
SRK - 3x3, Through Hole	10	None - Flush	None - Vertical	C - Complementary	None - No Tape	None - Tube
SRM - 2x3, SMT	16	H - Extended				
SRT - 4x1, Through Hole						
		For SRK Series:	For SRT Series:		For SRM Series:	For SRJ, SRK, and SRT Series:
		10	None - Vertical		None - No Tape	None - Tube
		16	R - Right Angle		T - Taped	TR - Tape and Reel
		For SRM and SRT Series:				
		10				
		16				



E-SWITCH®

www.e-switch.com

800.867.2717

DIP