







Extruded heatsinks for PCB mounting

- for semiconductor clip-mounting
- special lengths and transistor drillings upon request
- **P** = raised retaining stud, **E** = mounting method





art. no.	l [mm]	R _{th} [K/W]	⌀
SK 104 25,4 ...	25.4	14	TO 220
SK 104 38,1 ...	38.1	11	TO 220
SK 104 50,8 ...	50.8	9	TO 220
SK 104 63,5 ...	63.5	8	TO 220

please indicate:

... mouting method

STC = with solder pin


STIC = with solder pin and insulating washer







STCB = with threaded bolt M3, brass

surface:

black anodised

- for semiconductor screw-mounting
- special lengths and transistor drillings on request
- **E** = mounting method





art. no.	l [mm]	R _{th} [K/W]	⌀
SK 104 25,4 ...	25.4	14	SOT 32/ TO 220/ TO 3 P
SK 104 38,1 ...	38.1	11	SOT 32/ TO 220/ TO 3 P
SK 104 50,8 ...	50.8	9	SOT 32/ TO 220/ TO 3 P
SK 104 63,5 ...	63.5	8	SOT 32/ TO 220/ TO 3 P

please indicate:

... mouting method

STS = with solder pin

STIS = with solder pins and insulating washer

STSB = with threaded bolt M3, brass

surface:

black anodised