


PRODUCT NO.
71753-550
71753-550LF

FCI CONFIDENTIAL



FCIconnect.com



NOTES:

- 1 MATERIAL:
 - 1.1 HEADER ASSY:
PLASTIC HOUSING: LCP UL94V-0 NATURAL (WHITE)
 - 1.2 EJECT MECHANISM ASSY:
PLASTIC GUIDE: POLYPHTHARAMID UL94V-0 BLACK
COVER PLATE: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
- 2 RECOMMENDED HOLD DOWN - 2mm SCREWS (95121-001) AND NUTS (92869-001).
RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406 ISO 1101		CARDBUS			
ltr	ecm no	dr	date	tolerances unless otherwise specified			title			
A	V61449	RHG	10/1/96	angles	linear	$.X \pm .3$	NON-EJECT SPACER ASSEMBLY			
B	V91269	CGC	5/25/99			$.XX \pm .13$				
C	V01769	TFG	8/22/00	$\pm 2^\circ$		$.XXX \pm .051$				
D	N08-0219	MZ	11/26/08	dr	R.GRAPE	10/1/96	dwg no			
				enr	D.BRANN	10/1/96	sheet 1 of 1 size			
				chr	D.BRANN	10/1/96	71753			
				appd	D.BRANN	10/1/96	type CUSTOMER Drawing			
sheet	revision	D								
index	sheet	1								

