





SPECIFICATION

**Material:** APM RUBRGLAS™ (transparent silicone rubber), polymer type, ASTM D1418.  
**Temperature Range:** -80° F to +400° F (-62° C to +204° C)  
**Operational Life:** 10,000 actuations (minimum).  
**Resistant to:** Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils.  
**Agency Recognition:** UL & ULC Recognized to UL Std. 50.  
**Shelf Life:** Excess of 25 years.



SECTION B-B

ALL DIMENSIONS IN INCHES[MM]

TOLERANCE, UNLESS OTHERWISE NOTED  $\pm 1/32$  [ $\pm 0.793$ ]

C	CHANGED FORMAT AND NOTE	DAN LAW	04.26.13
B	CHANGE DWG# FROM C1113/66 to 1113/66, REVISED TITLE FOR ACCURACY		07.22.08
A	CAD COMPUTER GENERATED		10.23.02
REV.	DESCRIPTION		
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	TITLE: <b>ROCKER SWITCH BOOT ONE POLE</b>	ENG. S. GOK	07.22.08
MAT'L: <b>RUBRGLAS™</b>		DWN. M.M.	02.21.86
FINISH: <b>TRANSPARENT</b>		CHKD. F. KONCHALSKI	04.26.13
	SCALE	DWG. NO.	
	1:1	<b>1113/66</b>	

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.

THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.