

6

5

4

3

2

1



MATERIAL AND FINISH

Insulator: Polycarbonate, UL-94V-0 rated
 Contacts: Brass, Tin Plated

D

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A/15 A
 Voltage rating: 250 VAC
 Insulation resistance: 100 Mohm min. at 500 VDC
 Dielectric withstanding voltage: 2000 VAC for one minute



RECOMMENDED
PANEL CUTOUT



C

ORDERING CODE:
 43R04-1 2
 1 2

- 1) COLOR
 1 = BLACK
 2 = GRAY

2) ELECTRICAL CIRCUIT CONFIGURATION

1 = 10A 250V 70°C	
15A 250V 70°C 2+GROUND	
2 = 10A 250V 120°C 15A 250V 120°C 2+GROUND	



REV	DATE	CHNG	CHNG APPR

TOLERANCE
UNLESS OTHERWISE SPECIFIED

X ± 1
XX ± 0.4
XXX ± 0.20

DRAWN BY	GQ	DATE: 10/05/01
CHECK BY	TD	DATE: 10/09/01
APPR BY	PB	DATE: 10/09/01

Power Dynamics, Inc.

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: 10A/15A IEC 60320 APPL. OUTLET; SOLDER TERMINALS; SIDE FLANGE, PANEL MOUNT

43R04-1X2X

SHEET
1 of 1

SIZE: A	ALL DIMENSIONS FOR REFERENCE ONLY DIMENSIONS ARE IN MILLIMETERS
SCALE: NTS	REV:

6

5

4

3

2

1



MATERIAL AND FINISH

Insulator: Polycarbonate, UL-94V-0 rated
 Contacts: Brass, Tin Plated

D

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A/15 A
 Voltage rating: 250 VAC
 Insulation resistance: 100 Mohm min. at 500 VDC
 Dielectric withstanding voltage: 2000 VAC for one minute





ORDERING CODE:
 43R04-2 2
 1 2

- 1) COLOR
 1 = BLACK
 2 = GRAY

2) ELECTRICAL CIRCUIT CONFIGURATION

- 1 = 10A 250V 70°C

 15A 250V 70°C
 2+GROUND
- 2 = 10A 250V 120°C
 15A 250V 120°C
 2+GROUND



RECOMMENDED
 PANEL CUTOUT

REVISIONS	
CHANGE	APPR
REV	DATE

TOLERANCE
 UNLESS OTHERWISE SPECIFIED

X ± 1
 XX ± 0.4
 XXX ± 0.20

DRAWN BY	GQ	DATE: 10/05/01
CHECK BY	TD	DATE: 10/10/01
APPR BY	PB	DATE: 10/10/01

Power Dynamics, Inc.

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: 10A/15A IEC 60320 APPL. OUTLET; SOLDER TERMINALS; CROSS FLANGE, PANEL MOUNT

43R04-2X2X

SHEET
1 of 1

SIZE: A
 SCALE: NTS
 ALL DIMENSIONS FOR REFERENCE ONLY
 DIMENSIONS ARE IN MILLIMETERS

REV:

6

5

4

3

2

1

MATERIAL AND FINISH

Insulator: Polycarbonate, UL-94V-0 rated
 Contacts: Brass, Tin Plated

D ELECTRICAL SPECIFICATIONS:

Current rating: 10 A/15 A
 Voltage rating: 250 VAC
 Insulation resistance: 100 Mohm min. at 500 VDC
 Dielectric withstanding voltage: 2000 VAC for one minute

C ORDERING CODE:

43R04-3 1 2 - 3

1) COLOR



- 1 = BLACK
- 2 = GRAY

2) ELECTRICAL CIRCUIT CONFIGURATION



- | | | |
|----------------------|--|--|
| 1 = 10A 250V 70°C | | |
| 15A 250V 70°C 2+GND | | |
| 2 = 10A 250V 120°C | | |
| 15A 250V 120°C 2+GND | | |

3) PANEL THICKNESS

REV	DATE	CHNG/CHK APPR



RECOMMENDED
PANEL CUTOUT



P/N	A	MAX. PANEL THICKNESS
43R04-3X2X-150	1.5	1.5
43R04-3X2X-200	2.0	2.0
43R04-3X2X-250	2.5	2.5

ADDITIONAL PANEL THICKNESS
AVAILABLE ON REQUEST

TOLERANCE
UNLESS OTHERWISE SPECIFIED
 X \pm 1
 XX \pm 0.4
 XXX \pm 0.20

DRAWN BY	GQ	DATE: 10/05/01
CHECK BY	TD	DATE: 10/09/01
APPR BY	PB	DATE: 10/09/01

Power Dynamics, Inc.
 Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: 10A/15A IEC 60320 APPL. OUTLET; SOLDER TERMINALS; SNAP-IN, PANEL MOUNT

43R04-3X2X-XXX

SHEET
1 of 1

SIZE: A	ALL DIMENSIONS FOR REFERENCE ONLY DIMENSIONS ARE IN MILLIMETERS
SCALE: NTS	REV:

6

5

4

3

2

1