


No.28AWG 7x0.127 Thinned Stranded Copper Conductor



Electrical & Physical Characteristics:

- Voltage Rating: 300V
- Temperature Rating: 105°C
- Dielectric Strength: 2. OKV 60Hz 1 Minute
- Conductor Resistance: 237/KM Max.
- Insulation Resistance: 100M /M Min. @500V DC
- Tensile Strength Before Aging: 1,500PSI
- Tensile Strength After Aging: 70% Min. (136°C*168H)
- Elongation Before Aging: 100% Min.
- Elongation After Aging: 65% Min. (136°C*168H)
- Deformation Test 50% Max. (121°C*1H)
- Cold Bend Test: -10°C*4H No Cracking
- Horizontal Flame Test: VW-1
- UL File No. E189529
- UL Style: 2651-VW-1

RoHS
Compliant

ITEM NO.

AWG28-50/F/300-R

TITLE

Flat Ribbon Cable - 50 Conductors
1.27MM Pitch, 300 Feet-13" Reel, Multicolor

Unit: MM

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
©Copyright 2011 by Assmann Electronic Components
All International Rights Reserved