

FPC-3130

Robust Box PC with Intel® Atom™ D2550 Platform



Features

- Ultra Low Power and Fanless & Cable Less Design
- Wide Range DC Power Input (10 ~ 32V)
- Smarter Ignition Power On/Off, Delay-time and Battery Low Voltage Protection
- Over-voltage and Reversed Power Input Protection
- Outside Accessible CFast and SIM Slots
- Dual DVI Port Output
- RS-485 Auto-flow Function
- Wide Operating Temperature (-20 ~ 70 °C)
- Easy Installation/Maintenance
- Intel® SSD Compatible

System

CPU	Soldered onboard Intel® Atom™ D2550 1.86GHz processor
Memory	1 x 204-pin DDR3 SO-DIMM socket, supporting 800/1066MHz SDRAM up to 4GB
Chipset	Intel® NM10 PCH
Graphics	Integrated Intel GMA 3650
ATA	1 x Serial ATA port with 300MB/s HDD transfer rate
LAN Chipset	2 x Realtek 8111 GbE controllers
Watchdog Timer	1~255 levels reset

I/O

Serial Port	2 x RS-232 ports/ 2 x RS-232/422/485 selectable ports with DB-44 pin connector
USB Port	6 x USB 2.0 ports
LAN	2 x RJ-45 ports for GbE
Video Port	1 x DVI-I female connector for Digital Video Output 1 x DVI-D female connector for Digital Video Output
Audio	Mic-in/Line-out/Line-out (6W pre-amplified)
Expansion Bus	1 x Mini-card slot interconnected with SIM card socket for optional WiFi or HSUPA module 1 x SIM card socket

Environmental

Operating Temp.	-20 ~ 70 °C (-4 ~ 158 °F), ambient w/ air flow
Storage Temp.	-40 ~ 85 °C (-40 ~ 185 °F)
Operating Humidity	10 ~ 95% @ 70 °C (non-condensing)
Vibration	3 Grms/5~500Hz/random operation
Shock	Operating 40G (11ms), Non-operating 80G with CFast/SSD

Qualification

Certification CE, FCC Class B

Power Requirement

Power Input DC 10~32V input (w/ 3-pin DC input terminal block)

Power Consumption Max. 30W

Storage

Type 1 x 2.5" drive bay for HDD/SSD
1 x CFast socket

Mechanical

Construction Aluminum alloy

Mounting Wall-mount/VESA-mount/Din rail mounting

Weight 1.89 kg (4.16 lb) (Bare-bone)

Dimensions (W x D x H) 252 x 199 x 33 mm (9.92" x 7.83" x 1.3")

OS Support

Windows XP Embedded / Windows XP Professional / Windows Embedded 7 Professional / Windows Embedded 7 Standard


Ordering Information

FPC-3130 Barebone system w/o storage device and memory



» Fanless Design

Dimensions



Unit: mm

Optional Accessories

PAC-P065W 19V/3.4A 65W AC/DC adapter kit



VMK-3100 VESA mount kit



CBL-7100-COM 4 x COM ports converter cable



DRK-001 Din rail kit of FPC series




WMK-3100 Wall-mount kit



Optional Configuration (CTOS* Kit)


SSD-25040 Intel® 2.5" 40GB SATAII SSD kit



HSPA-SI1400 HSUPA 3.75G module kit & internal wiring




WIFI-IN1300 Intel® Centrino® Advanced-N 6205 WiFi module w/ 20cm internal wiring



ANT-D11 1 x WiFi Dual-band 2.4G/5G antenna



ANT-H11 1 x 2dBi HSUPA antenna



2GB SO-DIMM DDR3-1333 2GB SDRAM

4GB SO-DIMM DDR3-1333 4GB SDRAM



*CTOS means Configure-to-Order Service.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ARBOR Technology:](#)

[FPC-3130](#)