



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'HSTT25-C4'

Your search criteria matched only one product, shown below

HSTT25-C4



- Flexible Ployolefin DRY-SHRINKTMHeat Shrink Tubing
- General Purpose heat shrink tubing for dry locations
 - Applications include insulating, protecting, harnessing and identifying wires.
 - Material Type: Crosslinked Polyolefin
 - Shrink Ratio: 2:1
 - Temperature Range: -67°F to 275°F (-55°C to 135°C)
 - Flammability Rating: Flame retardant EXCEPT clear
 - Voltage: 600 V
 - UL Recognized, CSA Certified
 - Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

	Part Number	HSTT25C4
	RoHS Compliance Status	Compliant
	Part Description	Thin Wall Polyolefin Heat Shrink
	Material	Polyolefin cross-linked
	Color	Yellow
	CSA Certified	Yes
	Military Specification	AMS-DTL-23053/5 Class 1
	UL Recognized	E122770
	CE Compliant	No
	CE Marking	No
	Flammability Rating	Flame Retardant
	Length Per Reel (ft.)	100
	Length Per Reel (m)	30.5
	Max. Recovered I.D. (In.)	.125
	Max. Recovered I.D. (mm)	3.2
	Min. Expanded I.D. (In.)	.250
	Min. Expanded I.D. (mm)	6.4
	Nominal Diameter / Size	.250
	Nominal Recovered Wall Thickness (In.)	.025
	Nominal Recovered Wall Thickness (mm)	.6
	Pricing Description	Heat Shrink Thin, .25"(6.4mm) Dia, Yellow
	Shrink Ratio	2:1
	Temperature Range	-67°F to 275°F (55°C to 135°C)
	Min. Order UOM	RL
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.