

## General Information

Extended Product Type:	OD1365
Product ID:	2CMA131041R1000
ABB Type Designation:	OD1365
EAN:	7392696310413
Catalog Description:	Active energy Cl. 1
Long Description:	Electricity meter, Active measurement, Direct connected, 1 phase, Class 1, Verified and approved according MID, IEC approval

## Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Electricity Meters for DIN Rail » Electricity Meters

## Ordering

EAN:	7392696310413
Minimum Order Quantity:	1 piece
Customs Tariff Number:	90283011

## Dimensions

Product Net Width:	36 mm
Product Net Height:	85 mm
Product Net Depth:	64 mm
Product Net Weight:	0.145 kg

## Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	36 mm
Package Level 1 Height:	64 mm
Package Level 1 Length:	85 mm
Package Level 1 Gross Weight:	0.168 kg
Package Level 1 EAN:	7392696310413

## Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	-----------------------------------------------------------------

## Additional Information

Accuracy:	Active energy Cl. 1 Active energy Cl. B
Additional Information:	Resettable register
Communication Interface:	IR port Pulse output
Connecting Capacity-Main Circuit:	Rigid 1 ... 16 mm <sup>2</sup>
Degree of Protection:	IP20
Enclosure Material:	Plastic
Frequency (f):	50 Hz 60 Hz
Function:	Electricity meter
IIT Publishing Status:	Level 0 - Information enabled
Meter Type:	Direct connected
Mounting Type:	DIN rail
Number of Phases:	1
Product Main Type:	OD
Product Name:	Electricity Meter
Rated Current (I <sub>n</sub> ):	65 A
Rated Voltage (U <sub>r</sub> ):	Phase-to-Neutral 220 ... 240 V
RoHS Date:	2008-01
Standards:	IEC 62052-11 IEC 62053-21 EN 50470-1 EN 50470-3

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">2CMC482016D0001</a>
---------------------------------	---------------------------------

## Classifications

E-nummer: 0981087

Object Classification Code: P

