




LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-11-004820	11MAR11	RK	HMR




RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.00254-0.00508 [.000100-.000200] BRIGHT TIN-LEAD OVER 0.00127 [.000050] NICKEL ENTIRE POST.
6. FINISH: 0.00254-0.00508 [.000100-.000200] MATTE TIN OVER 0.00127 [.000050] NICKEL ENTIRE POST.

6	101.19 [3.984]	99.06 [3.900]	39	80	9-146505-0
6	98.65 [3.884]	96.52 [3.800]	38	78	8-146505-9
6	96.11 [3.784]	93.98 [3.700]	37	76	8-146505-8
6	93.57 [3.684]	91.44 [3.600]	36	74	8-146505-7
6	91.03 [3.584]	88.90 [3.500]	35	72	8-146505-6
6	88.49 [3.484]	86.36 [3.400]	34	70	8-146505-5
6	85.95 [3.384]	83.82 [3.300]	33	68	8-146505-4
6	83.41 [3.284]	81.28 [3.200]	32	66	8-146505-3
6	80.87 [3.184]	78.74 [3.100]	31	64	8-146505-2
6	78.33 [3.084]	76.20 [3.000]	30	62	8-146505-1
6	75.79 [2.984]	73.66 [2.900]	29	60	8-146505-0
6	73.25 [2.884]	71.12 [2.800]	28	58	7-146505-9
6	70.71 [2.784]	68.58 [2.700]	27	56	7-146505-8
6	68.17 [2.684]	66.04 [2.600]	26	54	7-146505-7
6	65.63 [2.584]	63.50 [2.500]	25	52	7-146505-6
6	63.09 [2.484]	60.96 [2.400]	24	50	7-146505-5
6	60.55 [2.384]	58.42 [2.300]	23	48	7-146505-4
6	58.01 [2.284]	55.88 [2.200]	22	46	7-146505-3
6	55.47 [2.184]	53.34 [2.100]	21	44	7-146505-2
6	52.93 [2.084]	50.80 [2.000]	20	42	7-146505-1
6	50.39 [1.984]	48.26 [1.900]	19	40	7-146505-0
6	47.85 [1.884]	45.72 [1.800]	18	38	6-146505-9
6	45.31 [1.784]	43.18 [1.700]	17	36	6-146505-8
6	42.77 [1.684]	40.64 [1.600]	16	34	6-146505-7
6	40.23 [1.584]	38.10 [1.500]	15	32	6-146505-6
6	37.69 [1.484]	35.56 [1.400]	14	30	6-146505-5
6	35.15 [1.384]	33.02 [1.300]	13	28	6-146505-4
6	32.61 [1.284]	30.48 [1.200]	12	26	6-146505-3
6	30.07 [1.184]	27.94 [1.100]	11	24	6-146505-2
6	27.53 [1.084]	25.40 [1.000]	10	22	6-146505-1
6	24.99 [.984]	22.86 [.900]	9	20	6-146505-0
6	22.45 [.884]	20.32 [.800]	8	18	5-146505-9
6	19.91 [.784]	17.78 [.700]	7	16	5-146505-8
6	17.37 [.684]	15.24 [.600]	6	14	5-146505-7
6	14.83 [.584]	12.70 [.500]	5	12	5-146505-6
6	12.29 [.484]	10.16 [.400]	4	10	5-146505-5
6	9.75 [.384]	7.62 [.300]	3	8	5-146505-4
6	7.21 [.284]	5.08 [.200]	2	6	5-146505-3
6	4.67 [.184]	2.54 [.100]	1	4	5-146505-2
6	2.13 [.084]	-	-	2	5-146505-1
PLATING	G	F	E	NO. OF NOISERS	PART NUMBER

5	101.19 [3.984]	99.06 [3.900]	39	80	4-146505-0
5	98.65 [3.884]	96.52 [3.800]	38	78	3-146505-9
5	96.11 [3.784]	93.98 [3.700]	37	76	3-146505-8
5	93.57 [3.684]	91.44 [3.600]	36	74	3-146505-7
5	91.03 [3.584]	88.90 [3.500]	35	72	3-146505-6
5	88.49 [3.484]	86.36 [3.400]	34	70	3-146505-5
5	85.95 [3.384]	83.82 [3.300]	33	68	3-146505-4
5	83.41 [3.284]	81.28 [3.200]	32	66	3-146505-3
5	80.87 [3.184]	78.74 [3.100]	31	64	3-146505-2
5	78.33 [3.084]	76.20 [3.000]	30	62	3-146505-1
5	75.79 [2.984]	73.66 [2.900]	29	60	3-146505-0
5	73.25 [2.884]	71.12 [2.800]	28	58	2-146505-9
5	70.71 [2.784]	68.58 [2.700]	27	56	2-146505-8
5	68.17 [2.684]	66.04 [2.600]	26	54	2-146505-7
5	65.63 [2.584]	63.50 [2.500]	25	52	2-146505-6
5	63.09 [2.484]	60.96 [2.400]	24	50	2-146505-5
5	60.55 [2.384]	58.42 [2.300]	23	48	2-146505-4
5	58.01 [2.284]	55.88 [2.200]	22	46	2-146505-3
5	55.47 [2.184]	53.34 [2.100]	21	44	2-146505-2
5	52.93 [2.084]	50.80 [2.000]	20	42	2-146505-1
5	50.39 [1.984]	48.26 [1.900]	19	40	2-146505-0
5	47.85 [1.884]	45.72 [1.800]	18	38	1-146505-9
5	45.31 [1.784]	43.18 [1.700]	17	36	1-146505-8
5	42.77 [1.684]	40.64 [1.600]	16	34	1-146505-7
5	40.23 [1.584]	38.10 [1.500]	15	32	1-146505-6
5	37.69 [1.484]	35.56 [1.400]	14	30	1-146505-5
5	35.15 [1.384]	33.02 [1.300]	13	28	1-146505-4
5	32.61 [1.284]	30.48 [1.200]	12	26	1-146505-3
5	30.07 [1.184]	27.94 [1.100]	11	24	1-146505-2
5	27.53 [1.084]	25.40 [1.000]	10	22	1-146505-1
5	24.99 [.984]	22.86 [.900]	9	20	1-146505-0
5	22.45 [.884]	20.32 [.800]	8	18	146505-9
5	19.91 [.784]	17.78 [.700]	7	16	146505-8
5	17.37 [.684]	15.24 [.600]	6	14	146505-7
5	14.83 [.584]	12.70 [.500]	5	12	146505-6
5	12.29 [.484]	10.16 [.400]	4	10	146505-5
5	9.75 [.384]	7.62 [.300]	3	8	146505-4
5	7.21 [.284]	5.08 [.200]	2	6	146505-3
5	4.67 [.184]	2.54 [.100]	1	4	146505-2
5	2.13 [.084]	-	-	2	146505-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. <u>BRANDBERG</u> 11-NOV-96		 TE Connectivity	
		CHK. <u>G. DUBNICZKI</u> 11-NOV-96			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm [INCHES]		APPROVED <u>G. DUBNICZKI</u> 11-NOV-96		HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SUB.POST, UNSHROUDED	
		PRODUCT SPEC		SIZE	
		APPLICATION SPEC		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
SEE TABLE		—		A1 00779 C-146505	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV A1	