

BTA2008 series D and E

0.8 A Three-quadrant triacs high commutation

Rev. 01 — 18 January 2008

Product data sheet

1. Product profile

1.1 General description

Passivated, guaranteed commutation, sensitive gate triacs in a SOT54 plastic package

1.2 Features

- Guaranteed commutation performance at each gate sensitivity
- Easily interfaced with low power drivers including microcontrollers
- Sensitive gate

1.3 Applications

- Motor control
- Solenoid drivers

1.4 Quick reference data

- $V_{DRM} \leq 600 \text{ V}$ (BTA2008-600D)
- $V_{DRM} \leq 600 \text{ V}$ (BTA2008-600E)
- $V_{DRM} \leq 800 \text{ V}$ (BTA2008-800D)
- $V_{DRM} \leq 800 \text{ V}$ (BTA2008-800E)
- $I_{TSM} \leq 9 \text{ A}$ ($t = 20 \text{ ms}$)
- $I_{GT} \leq 5 \text{ mA}$ (BTA2008-600D)
- $I_{GT} \leq 5 \text{ mA}$ (BTA2008-800D)
- $I_{GT} \leq 10 \text{ mA}$ (BTA2008-600E)
- $I_{GT} \leq 10 \text{ mA}$ (BTA2008-800E)
- $I_{T(RMS)} \leq 0.8 \text{ A}$

2. Pinning information

Table 1. Pinning

Pin	Description	Simplified outline	Graphic symbol
1	main terminal 2 (T2)	<p>SOT54 (TO-92)</p>	<p>sym051</p>
2	gate (G)		
3	main terminal 1 (T1)		

3. Ordering information

Table 2. Ordering information

Type number	Package		Version
	Name	Description	
BTA2008-600D	TO-92	plastic single-ended leaded (through hole) package; 3 leads	SOT54
BTA2008-600E			
BTA2008-800D			
BTA2008-800E			

4. Limiting values

Table 3. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DRM}	repetitive peak off-state voltage	BTA2008-600D; BTA2008-600E	[1] -	600	V
		BTA2008-800D; BTA2008-800E	-	800	V
$I_{\text{T(RMS)}}$	RMS on-state current	full sine wave; $T_{\text{lead}} \leq 70\text{ }^{\circ}\text{C}$; see Figure 4 and 5	-	0.8	A
I_{TSM}	non-repetitive peak on-state current	full sine wave; $T_{\text{j}} = 25\text{ }^{\circ}\text{C}$ prior to surge; see Figure 2 and 3			
		$t = 20\text{ ms}$	-	9	A
		$t = 16.7\text{ ms}$	-	9.9	A
I^2t	I^2t for fusing	$t_{\text{p}} = 10\text{ ms}$	-	0.41	A^2s
di_{T}/dt	rate of rise of on-state current	$I_{\text{TM}} = 1.5\text{ A}$; $I_{\text{G}} = 20\text{ mA}$; $di_{\text{G}}/dt = 0.2\text{ A}/\mu\text{s}$	-	100	$\text{A}/\mu\text{s}$
I_{GM}	peak gate current		-	1	A
P_{GM}	peak gate power		-	5	W
$P_{\text{G(AV)}}$	average gate power	over any 20 ms period	-	0.1	W
T_{stg}	storage temperature		-40	+150	$^{\circ}\text{C}$
T_{j}	junction temperature		-	125	$^{\circ}\text{C}$

- [1] Although not recommended, off-state voltages up to 800 V may be applied without damage, but the triac may switch to the on-state. The rate of rise of current should not exceed 6 A/ μs .




Fig. 1. Total power dissipation as a function of RMS on-state current; maximum values






Fig. 2. Non-repetitive peak on-state current as a function of the number of sinusoidal current cycles; maximum values



$t_p \leq 20\text{ ms}$
(1) di_T/dt limit

Fig 3. Non-repetitive peak on-state current as a function of pulse duration; maximum values



$f = 50\text{ Hz}$
 $T_{lead} = 70\text{ }^{\circ}\text{C}$

Fig 4. RMS on-state current as a function of surge duration; maximum values




Fig 5. RMS on-state current as a function of lead temperature; maximum values

5. Thermal characteristics

Table 4. Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$R_{th(j-lead)}$	thermal resistance from junction to lead	full cycle; see Figure 6	-	-	60	K/W
$R_{th(j-a)}$	thermal resistance from junction to ambient	printed circuit board mounted; lead length 4 mm	-	150	-	K/W




Fig 6. Transient thermal impedance from junction to lead as a function of pulse duration

6. Static characteristics

Table 5. Static characteristics



$T_j = 25\text{ °C}$ unless otherwise specified.


Symbol	Parameter	Conditions	BTA2008-600D BTA2008-800D			BTA2008-600E BTA2008-800E			Unit
			Min	Typ	Max	Min	Typ	Max	
I_{GT}	gate trigger current	$V_D = 12\text{ V}$; $I_T = 0.1\text{ A}$; see Figure 8							
		T2+ G+	0.25	-	5	0.5	-	10	mA
		T2+ G-	0.25	-	5	0.5	-	10	mA
		T2- G-	0.25	-	5	0.5	-	10	mA
I_L	latching current	$V_D = 12\text{ V}$; $I_{GT} = 0.1\text{ A}$; see Figure 10							
		T2+ G+	-	-	10	-	-	12	mA
		T2+ G-	-	-	20	-	-	20	mA
		T2- G-	-	-	10	-	-	12	mA
I_H	holding current	$V_D = 12\text{ V}$; $I_{GT} = 0.1\text{ A}$; see Figure 11	-	-	10	-	-	12	mA
V_T	on-state voltage	$I_T = 0.85\text{ A}$; see Figure 9	-	1.35	1.6	-	1.35	1.6	V
V_{GT}	gate trigger voltage	$V_D = 12\text{ V}$; $I_T = 0.1\text{ A}$; see Figure 7	-	0.9	2	-	0.9	2	V
		$V_D = 400\text{ V}$; $I_T = 0.1\text{ A}$; $T_j = 125\text{ °C}$	0.2	0.3	-	0.2	0.3	-	V
I_D	off-state current	$V_D = V_{DRM(max)}$; $T_j = 125\text{ °C}$	-	0.1	0.5	-	0.1	0.5	mA

7. Dynamic characteristics

Table 6. Dynamic characteristics

Symbol	Parameter	Conditions	BTA2008-600D BTA2008-800D			BTA2008-600E BTA2008-800E			Unit
			Min	Typ	Max	Min	Typ	Max	
dV_D/dt	rate of rise of off-state voltage	$V_{DM} = 0.67 \times V_{DRM(max)}$; $T_j = 125\text{ }^{\circ}\text{C}$; exponential waveform; gate open circuit	200	-	-	600	-	-	V/ μs
dI_{com}/dt	rate of change of commutating current	$V_{DM} = 400\text{ V}$; $T_j = 125\text{ }^{\circ}\text{C}$; $I_{T(RMS)} = 0.8\text{ A}$; $dV/dt = 10\text{ V}/\mu\text{s}$; gate open circuit	0.5	-	-	1.6	-	-	A/ms
t_{gt}	gate-controlled turn-on time	$I_{TM} = 1\text{ A}$; $V_D = V_{DRM(max)}$; $I_G = 0.1\text{ A}$; $dI_G/dt = 5\text{ A}/\mu\text{s}$	-	2	-	-	2	-	μs





- $V_o = 0.835$ V
 $R_s = 0.5$ Ω
- (1) $T_j = 125$ °C; typical values
 - (2) $T_j = 125$ °C; maximum values
 - (3) $T_j = 25$ °C; maximum values

Fig 9. On-state current as a function of on-state voltage




Fig 10. Normalized latching current as a function of junction temperature




Fig 11. Normalized holding current as a function of junction temperature

8. Package outline

Plastic single-ended leaded (through hole) package; 3 leads

SOT54




Fig 12. Package outline SOT54 (TO-92)

9. Revision history

Table 7. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BTA2008_SER_D_E_1	20080118	Product data sheet	-	-

10. Legal information

10.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

10.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

10.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

10.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

11. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

12. Contents

1 Product profile 1

1.1 General description..... 1

1.2 Features 1

1.3 Applications 1

1.4 Quick reference data..... 1

2 Pinning information..... 1

3 Ordering information..... 2

4 Limiting values..... 2

5 Thermal characteristics..... 5

6 Static characteristics..... 6

7 Dynamic characteristics 7

8 Package outline 9

9 Revision history..... 10

10 Legal information..... 11

10.1 Data sheet status 11

10.2 Definitions 11

10.3 Disclaimers 11

10.4 Trademarks..... 11

11 Contact information..... 11

12 Contents 12



Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NXP:](#)

[BTA2008-600D,412](#) [BTA2008-600E,412](#) [BTA2008-800D,412](#) [BTA2008-800E,412](#)