



1305




1305-0-15-XX-47-XX-04-0
Press-fit in 1,55 mounting hole

1306



1306-0-15-XX-47-XX-04-0
Press-fit in 1,55 mounting hole.


7305



7305-0-15-XX-47-XX-10-0


Solder mount in 1,52 min. mounting hole
Also available on 8mm wide carrier
tape: 6,000 parts per 330mm reel.
Order as: 7305-0-57-XX-47-XX-10-0

0400




0400-0-15-XX-47-XX-04-0
Press-fit in 1,7 mounting hole.

0335




0335-0-15-XX-47-XX-04-0
Hex press-fit in .1,63
plated thru hole

4614




4614-0-31-XX-47-XX-04-0
Compliant press-fit in 1,02±0,08 plated
hole. For 1,52→2,54 thick board.

4615




4615-0-31-XX-47-XX-04-0
Compliant press-fit in 1,02±0,08 plated
hole. For 2,29→3,30 thick board.

7614




7614-0-31-XX-47-XX-04-0
Compliant press-fit in 1,02±0,08 plated
hole. For 1,52→2,54 thick board.

8401




8401-0-15-XX-47-XX-04-0
Hex press-fit in 1,6
plated thru hole

2400




2400-0-15-XX-47-XX-04-0
Press-fit in 1,68 mounting hole.

6857



6857-0-15-XX-47-XX-10-0
Press-fit in 1,57 mounting hole.

9393



9393-0-15-XX-47-XX-10-0
Press-fit in 1,70 mounting hole.

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±0,13
DIAMETERS: ±0,05
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - 47 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◇ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◇ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◇ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◇ 27 0,76µm GOLD OVER NICKEL (RoHS)



CONTACT

#47 CONTACT (DATA ON PAGE 222)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[9393-0-15-01-47-01-10-0](#) [9393-0-15-01-47-27-10-0](#) [6857-0-15-01-47-01-10-0](#) [6857-0-15-01-47-27-10-0](#) [9393-0-15-80-47-80-10-0](#) [9393-0-15-80-47-27-10-0](#) [6857-0-15-80-47-80-10-0](#) [6857-0-15-80-47-27-10-0](#) [9393-0-15-15-47-27-10-0](#)