





6030, ML8



Model	Material	R_{θ} ($^{\circ}\text{C/W}$)
6030B	Al	12.5
6030PB	Al	12.5
ML8*	Al	12.5

* Fins on the ML8 are the twisted vane configuration.




6021, 6221





Model	Dim. A mm (inches)	Dim. B mm (inches)	Dim. C mm (inches)	R_{θ} ($^{\circ}\text{C/W}$)
6021PB	2.21 $\pm$.13 (.087 $\pm$.005)	10.16 (.400)	1.78 (.070)	12.5
6221PB	3.18 $\pm$.13 (.125 $\pm$.005)	6.99 (.275)	2.54 (.100)	12.5

U.S. Patent No. D.260,388



▲ 6021PB



▲ Hole pattern shown for 6021 only. See Figure 1 for slot detail used on 6221 only.

▲ FIGURE 1

TV65, TV71



TV65



TV71





Model	R_{θ} ($^{\circ}\text{C/W}$)
TV65	13.5
TV71	13.5



▲ TV65



▲ TV71



Cut-out in TV71 only, 11mm. x 11mm.