


FED. MFG. CODE 91929

CATALOG LISTING
602EN109-R★





14


04JUN08

FO-02851-A

RAWN



8- HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
9- CONNECTOR MUST BE PARALLEL WITH CENTERLINE OF
BUSHING KEYWAY WITHIN $\pm 6^\circ$

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		THIRD ANGLE PROJECTION 		SCALE FULL																																				
CHARACTERISTICS		ELECTRICAL DATA		DO NOT SCALE PRINT																																				
OPERATING FORCE ----- 6-12 LB		CONTACT ARRANGEMENT		TOLERANCES																																				
FULL OVERTRAVEL FORCE ----- 30. LB MAX		SPDT (2)		APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2																																				
RELEASE FORCE ----- 4 LB MIN		28 VDC		<table><tr><th></th><th>DIM.</th><th>TOL.</th><th>DIM.</th><th>TOL.</th></tr><tr><th></th><th>IN.</th><th>MM</th><th>IN.</th><th>MM</th></tr><tr><td>NO PLACES</td><td></td><td></td><td></td><td></td></tr><tr><td>ONE PLACE</td><td>±.004</td><td>±.004</td><td>±.004</td><td>±.004</td></tr><tr><td>TWO PLACES</td><td>±.005</td><td>±.005</td><td>±.005</td><td>±.005</td></tr><tr><td>THREE PLACES</td><td>±.006</td><td>±.006</td><td>±.006</td><td>±.006</td></tr><tr><td>ANGLES</td><td></td><td></td><td></td><td></td></tr></table>			DIM.	TOL.	DIM.	TOL.		IN.	MM	IN.	MM	NO PLACES					ONE PLACE	±.004	±.004	±.004	±.004	TWO PLACES	±.005	±.005	±.005	±.005	THREE PLACES	±.006	±.006	±.006	±.006	ANGLES				
	DIM.	TOL.	DIM.	TOL.																																				
	IN.	MM	IN.	MM																																				
NO PLACES																																								
ONE PLACE	±.004	±.004	±.004	±.004																																				
TWO PLACES	±.005	±.005	±.005	±.005																																				
THREE PLACES	±.006	±.006	±.006	±.006																																				
ANGLES																																								
PRETRAVEL ----- .040 MAX		LOAD		<table><tr><th></th><th>IN</th><th>MM</th></tr><tr><td>NO PLACES</td><td></td><td></td></tr><tr><td>ONE PLACE</td><td>±.004</td><td>±.004</td></tr><tr><td>TWO PLACES</td><td>±.005</td><td>±.005</td></tr><tr><td>THREE PLACES</td><td>±.006</td><td>±.006</td></tr><tr><td>ANGLES</td><td></td><td></td></tr></table>			IN	MM	NO PLACES			ONE PLACE	±.004	±.004	TWO PLACES	±.005	±.005	THREE PLACES	±.006	±.006	ANGLES																			
	IN	MM																																						
NO PLACES																																								
ONE PLACE	±.004	±.004																																						
TWO PLACES	±.005	±.005																																						
THREE PLACES	±.006	±.006																																						
ANGLES																																								
DIFFERENTIAL TRAVEL ----- .020 MAX		SEA LEVEL		US CUSTOMARY																																				
OVERTRAVEL ----- .210 MIN		50,000 FT.		DESIGN UNITS ☐ ☒																																				
		RES 7		RAW MATERIAL-COMMERCIAL STANDARD MICRO SWITCH STANDARDS APPLY																																				
		IND 4		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED																																				
		MOTOR 4		WEIGHT .10 LBS MAX																																				
		LAMP																																						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[602EN109-R](#)