

Technical Data

Issue 9 / May 2006

AT20 PVC Extra Heavy Duty Pipewrap Tape

General description

A heavy duty PVC film coated with a clear, anti-corrosive, aggressive adhesive.

- Flame retardant
- Self-extinguishing
- Flexible
- Conformable to awkward shapes
- Water resistant
- Very high abrasion resistance
- UV resistant
- Non-corrosive adhesive
- Extra heavy duty



Technical Details

Typical values

Thickness	0.440mm
Breaking Load	90 N/cm
Elongation	200%
Adhesion	
Steel	3.0 N/cm
Self	2.6 N/cm
Flame Retardancy	Self extinguishing
Water Extract	
pH	6.0 to 8.0
Conductivity	Max. 2.5 mS/m
B/down Voltage	12 kV
RoHS Compliant	Yes
Service Temperature	+5°C to +80°C
Application Temperature	+5°C to +40°C
Storage Temperature	+12°C to +25°C

NOTE

Except where indicated otherwise, the figures stated are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

 **ADVANCE**
adhesive tapes



AFERA

Association des Fabricants Européens de
Rubans Auto-Adhésifs.

Advance Tapes International Limited, PO Box 122,
Abbey Meadows, Leicester, LE4 5RA.
Tel: 0116 251 0191. Fax: 0116 265 2046. www.advancetapes.com