

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O.
LOW TEMPERATURE: COLOR BLUE.
HIGH TEMPERATURE: COLOR GREY OR BLACK.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS

EXAMPLE: 8 POS: (Nx2.54)-0.08=20.24 mm
5 - HE13 PRINTING ON 75915-3xx PRODUCT.
6 - ROHS COMPATIBLE PRODUCT SPECIFICATIONS

"LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b – MANUFACTURING PROCESS COMPATIBILITY



- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

C – LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004


7 - PRINTING & HOLE PATTERN SEE NEXT SHEET.



PDS: Rev :AG STATUS:Released Printed: Oct 29, 2014

A

A



B

B

C

C

mat'l. code SEE SHEET 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX												
ltr	ecn no	dr	date	tolerances unless otherwise specified					title													
A	F04-0347	DLE	04.09.23	angles linear		±0.3		mm 		BtB RECEPT. VERT SR TMT												
B	F05-0230	DLE	05.08.08																			
C	F06-0204	DLE	06.06.20			±2'																
D	F07-0109	DLE	07.01.16	dr	D.LEGRAND		04.09.23				dwg no				sheet 2 of -				size			
				enr	P.NIZZI		04.09.23				75915				A4							
				chr	D.LEGRAND		04.09.23															
				appd	P.NIZZI		04.09.23															
sheet index		revision sheet																				

D

D