






OPTION B
SAME AS OPTION A
EXCEPT AS SHOWN

CKT	DIM A	DIM B	DIM L	DIM M	DIM N
06	12.70 .500	5.08 .200	3.81 .150	3.81 .150	—
08	15.24 .600	7.62 .300	3.81 .150	3.81 .150	—
10	17.78 .700	10.16 .400	3.81 .150	6.35 .250	—
12	20.32 .800	12.70 .500	3.81 .150	6.35 .250	—
14	22.86 .900	15.24 .600	3.81 .150	8.89 .350	—
16	25.40 1.000	17.78 .700	3.81 .150	8.89 .350	—
18	27.94 1.100	20.32 .800	3.81 .150	11.43 .450	—
20	30.48 1.200	22.86 .900	3.81 .150	3.81 .150	21.59 .850
22	33.02 1.300	25.40 1.000	3.81 .150	3.81 .150	24.13 .950
24	35.56 1.400	27.94 1.100	3.81 .150	3.81 .150	26.67 1.050
26	38.10 1.500	30.48 1.200	3.81 .150	3.81 .150	29.21 1.150
28	40.64 1.600	33.02 1.300	3.81 .150	3.81 .150	31.75 1.250
30	43.18 1.700	35.56 1.400	3.81 .150	3.81 .150	34.29 1.350
32	45.72 1.800	38.10 1.500	3.81 .150	3.81 .150	36.83 1.450
34	48.26 1.900	40.64 1.600	3.81 .150	3.81 .150	39.37 1.550
36	50.80 2.000	43.18 1.700	3.81 .150	3.81 .150	41.91 1.650
38	53.34 2.100	45.72 1.800	3.81 .150	3.81 .150	44.45 1.750
40	55.88 2.200	48.26 1.900	3.81 .150	3.81 .150	46.99 1.850
42	58.42 2.300	50.80 2.000	3.81 .150	3.81 .150	49.53 1.950
44	60.96 2.400	53.34 2.100	3.81 .150	3.81 .150	52.07 2.050
46	63.50 2.500	55.88 2.200	3.81 .150	3.81 .150	54.61 2.150
48	66.04 2.600	58.42 2.300	3.81 .150	3.81 .150	57.15 2.250
50	68.58 2.700	60.96 2.400	3.81 .150	3.81 .150	59.69 2.350
52	71.12 2.800	63.50 2.500	3.81 .150	3.81 .150	62.23 2.450
54	73.66 2.900	66.04 2.600	3.81 .150	3.81 .150	64.77 2.550
56	76.20 3.000	68.58 2.700	3.81 .150	3.81 .150	67.31 2.650
58	78.74 3.100	71.12 2.800	3.81 .150	3.81 .150	69.85 2.750
60	81.28 3.200	73.66 2.900	3.81 .150	3.81 .150	72.32 2.850
62	83.82 3.300	76.20 3.000	3.81 .150	3.81 .150	74.93 2.950
64	86.36 3.400	78.74 3.100	3.81 .150	3.81 .150	77.47 3.050
66	88.90 3.500	81.28 3.200	3.81 .150	3.81 .150	80.01 3.150
68	91.44 3.600	83.82 3.300	3.81 .150	3.81 .150	82.55 3.250
70	93.98 3.700	86.36 3.400	3.81 .150	3.81 .150	85.09 3.350
72	96.52 3.800	88.90 3.500	3.81 .150	3.81 .150	87.63 3.450

SEE SHEET 1 EC NO: UCP2017-1310 DRWN:KSM/EC CHKD: APPR:FSM/TH	2016/12/12 2016/12/21	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	4 SIDES SHROUDED HEADER HIGH TEMP, (2.54)/.100 GRID W/ (.064)/.025 PINS MOLEX INCORPORATED
					mm	INCH	DRAWN BY EIK	DATE 1988/03/10	TITLE		
				4 PLACES	± ---	± ---	CHECKED BY EIK	DATE 1988/03/10			
				3 PLACES	± ---	± .005	APPROVED BY SMILLER	DATE 2010/03/31			
				2 PLACES	± 0.13	± .010	MATERIAL NO.		DOCUMENT NO.		
				1 PLACE	± 0.25	± ---	SEE TABLE		SDA-70567-****		
				ANGULAR ±1/2°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
SHEET NO. 2 OF 5											

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
H	ENGINEERING NUMBER A-70567	MANUFACTURE RELEASE STATUS					E REF.	C ±.015 (0.38)				CONNECTOR END PLATING		P.C. BOARD END PLATING		PACKAGING INFORMATION PK-T0873-				
												TYPE		D MEAS.	TYPE	F MEAS.				
L	-0001/-0034	R.F.M.					.130 (3.30)	.315 (8.00)				TIN		.100 (2.54)	TIN	.050 (1.27)	0018			
	-0035/-0068	R.F.M.					.200 (5.08)	.315 (8.00)				TIN		.100 (2.54)	TIN	.050 (1.27)	0018			
	-0069/-0102	R.F.M.					.130 (3.30)	.315 (8.00)				15 GOLD		.100 (2.54)	TIN	.050 (1.27)	0018			
	-0103/-0136	R.F.M.					.200 (5.08)	.315 (8.00)				15 GOLD		.100 (2.54)	TIN	.050 (1.27)	0018			
K	-0137/-0170	R.F.M.					.130 (3.30)	.315 (8.00)				30 GOLD		.100 (2.54)	TIN	.050 (1.27)	0018			
	-0171/-0204	R.F.M.					.200 (5.08)	.315 (8.00)				30 GOLD		.100 (2.54)	TIN	.050 (1.27)	0018			
J																				

NO. OF CKTS	OPTION "A"			OPTION "A"			OPTION "A"			OPTION "A"			OPTION "A"			OPTION "A"						NO. OF CKTS
	EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		EDP NUMBER	ENG NUMBER		
06	15-80-0061	A-70567-0001		70567-0035	A-70567-0035		15-80-0063	A-70567-0069		70567-0103	A-70567-0103		15-80-0065	A-70567-0137		70567-0171	A-70567-0171					06
08	15-80-0081	A-70567-0002		70567-0036	A-70567-0036		15-80-0083	A-70567-0070		70567-0104	A-70567-0104		15-80-0085	A-70567-0138		70567-0172	A-70567-0172					08
10	15-80-0101	A-70567-0003		70567-0037	A-70567-0037		15-80-0103	A-70567-0071		70567-0105	A-70567-0105		15-80-0105	A-70567-0139		70567-0173	A-70567-0173					10
12	15-80-0121	A-70567-0004		70567-0038	A-70567-0038		15-80-0123	A-70567-0072		70567-0106	A-70567-0106		15-80-0125	A-70567-0140		70567-0174	A-70567-0174					12
14	15-80-0141	A-70567-0005		70567-0039	A-70567-0039		15-80-0143	A-70567-0073		70567-0107	A-70567-0107		15-80-0145	A-70567-0141		70567-0175	A-70567-0175					14
16	15-80-0161	A-70567-0006		70567-0040	A-70567-0040		15-80-0163	A-70567-0074		70567-0108	A-70567-0108		15-80-0165	A-70567-0142		70567-0176	A-70567-0176					16
18	15-80-0181	A-70567-0007		70567-0041	A-70567-0041		15-80-0183	A-70567-0075		70567-0109	A-70567-0109		15-80-0185	A-70567-0143		70567-0177	A-70567-0177					18
20	15-80-0201	A-70567-0008		70567-0042	A-70567-0042		15-80-0203	A-70567-0076		70567-0110	A-70567-0110		15-80-0205	A-70567-0144		70567-0178	A-70567-0178					20
22	15-80-0221	A-70567-0009		70567-0043	A-70567-0043		15-80-0223	A-70567-0077		70567-0111	A-70567-0111		15-80-0225	A-70567-0145		70567-0179	A-70567-0179					22
24	15-80-0241	A-70567-0010		70567-0044	A-70567-0044		15-80-0243	A-70567-0078		70567-0112	A-70567-0112		15-80-0245	A-70567-0146		70567-0180	A-70567-0180					24
26	15-80-0261	A-70567-0011		70567-0045	A-70567-0045		15-80-0263	A-70567-0079		70567-0113	A-70567-0113		15-80-0265	A-70567-0147		70567-0181	A-70567-0181					26
28	15-80-0281	A-70567-0012		70567-0046	A-70567-0046		15-80-0283	A-70567-0080		70567-0114	A-70567-0114		15-80-0285	A-70567-0148		70567-0182	A-70567-0182					28
30	15-80-0301	A-70567-0013		70567-0047	A-70567-0047		15-80-0303	A-70567-0081		70567-0115	A-70567-0115		15-80-0305	A-70567-0149		70567-0183	A-70567-0183					30
32	15-80-0321	A-70567-0014		70567-0048	A-70567-0048		15-80-0323	A-70567-0082		70567-0116	A-70567-0116		15-80-0325	A-70567-0150		70567-0184	A-70567-0184					32
34	15-80-0341	A-70567-0015		70567-0049	A-70567-0049		15-80-0343	A-70567-0083		70567-0117	A-70567-0117		15-80-0345	A-70567-0151		70567-0185	A-70567-0185					34
36	15-80-0361	A-70567-0016		70567-0050	A-70567-0050		15-80-0363	A-70567-0084		70567-0118	A-70567-0118		15-80-0365	A-70567-0152		70567-0186	A-70567-0186					36
38	15-80-0381	A-70567-0017		70567-0051	A-70567-0051		15-80-0383	A-70567-0085		70567-0119	A-70567-0119		15-80-0385	A-70567-0153		70567-0187	A-70567-0187					38
40	15-80-0401	A-70567-0018		70567-0052	A-70567-0052		15-80-0403	A-70567-0086		70567-0120	A-70567-0120		15-80-0405	A-70567-0154		70567-0188	A-70567-0188					40
42	15-80-0421	A-70567-0019		70567-0053	A-70567-0053		15-80-0423	A-70567-0087		70567-0121	A-70567-0121		15-80-0425	A-70567-0155		70567-0189	A-70567-0189					42
44	15-80-0441	A-70567-0020		70567-0054	A-70567-0054		15-80-0443	A-70567-0088		70567-0122	A-70567-0122		15-80-0445	A-70567-0156		70567-0190	A-70567-0190					44
46	15-80-0461	A-70567-0021		70567-0055	A-70567-0055		15-80-0463	A-70567-0089		70567-0123	A-70567-0123		15-80-0465	A-70567-0157		70567-0191	A-70567-0191					46
48	15-80-0481	A-70567-0022		70567-0056	A-70567-0056		15-80-0483	A-70567-0090		70567-0124	A-70567-0124		15-80-0485	A-70567-0158		70567-0192	A-70567-0192					48
50	15-80-0501	A-70567-0023		70567-0057	A-70567-0057		15-80-0503	A-70567-0091		70567-0125	A-70567-0125		15-80-0505	A-70567-0159		70567-0193	A-70567-0193					50
52	15-80-0521	A-70567-0024		70567-0058	A-70567-0058		15-80-0523	A-70567-0092		70567-0126	A-70567-0126		15-80-0525	A-70567-0160		70567-0194	A-70567-0194					52
54	15-80-0541	A-70567-0025		70567-0059	A-70567-0059		15-80-0543	A-70567-0093		70567-0127	A-70567-0127		15-80-0545	A-70567-0161		70567-0195	A-70567-0195					54
56	15-80-0561	A-70567-0026		70567-0060	A-70567-0060		15-80-0563	A-70567-0094		70567-0128	A-70567-0128		15-80-0565	A-70567-0162		70567-0196	A-70567-0196					56
58	15-80-0581	A-70567-0027		70567-0061	A-70567-0061		15-80-0583	A-70567-0095		70567-0129	A-70567-0129		15-80-0585	A-70567-0163		70567-0197	A-70567-0197					58
60	15-80-0601	A-70567-0028		70567-0062	A-70567-0062		15-80-0603	A-70567-0096		70567-0130	A-70567-0130		15-80-0605	A-70567-0164		70567-0198	A-70567-0198					60
62	15-80-0621	A-70567-0029		70567-0063	A-70567-0063		15-80-0623	A-70567-0097		70567-0131	A-70567-0131		15-80-0625	A-70567-0165		70567-0199	A-70567-0199					62
64	15-80-0641	A-70567-0030		70567-0064	A-70567-0064		15-80-0643	A-70567-0098		70567-0132	A-70567-0132		15-80-0645	A-70567-0166		70567-0200	A-70567-0200					64
66	15-80-0661	A-70567-0031		70567-0065	A-70567-0065		15-80-0663	A-70567-0099		70567-0133	A-70567-0133		15-80-0665	A-70567-0167		70567-0201	A-70567-0201					66
68	15-80-0681	A-70567-0032		70567-0066	A-70567-0066		15-80-0683	A-70567-0100		70567-0134	A-70567-0134		15-80-0685	A-70567-0168		70567-0202	A-70567-0202					68
70	15-80-0701	A-70567-0033		70567-0067	A-70567-0067		15-80-0703	A-70567-0101		70567-0135	A-70567-0135		15-80-0705	A-70567-0169		70567-0203	A-70567-0203					70
72	15-80-0721	A-70567-0034		70567-0068	A-70567-0068		15-80-0723	A-70567-0102		70567-0136	A-70567-0136		15-80-0725	A-70567-0170		70567-0204	A-70567-0204					72

SEE SHEETS 1 & 2 EC NO: UCP2017-1310 DRAWN: SAMIEC CHKD: APPROV: SMITH REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLES		SHEET NO.		
		mm	INCH	DRAWN BY	DATE	4 SIDES SHROUDED HEADER			HIGH TEMP. (2.54)/.100		3 OF 5		
		4 PLACES ±.005	±.005	CHECKED BY	DATE	GRID W/ (.064)/.025 PINS			MOLEX INCORPORATED				
		2 PLACES ±0.13	±.010	APPROVED BY	DATE	1 PLACE ±0.25			SDA-70567-****				
		ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

J

H

C

B



tb_frame_C_P_AM_T
Rev. F 2009/06/18