

## SUPDM56HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDM56HW**



### Description

The SUPDM56HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U and SU6000RT4U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 120/208 or 120/240 VAC split-phase power. Detachable hardwire module allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

### Features

- The SUPDM56HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U and SU6000RT4U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 120/208 or 120/240 VAC split-phase power
- Detachable hardwire module allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

### Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with input voltages of 120/208 or 120/240 VAC split-phase power
- Convenient quick-disconnect terminal block allows installation in minutes

### Applications

- Use with Tripp Lite SU5000RT4U and SU6000RT4U UPS systems in 120, 208/240V applications where hardwire input/output connections are required

### System Requirements

- Use with SU5000RT4U and SU6000RT4U split-phase SmartOnline Hot-Swappable Modular UPS Systems

### Package Includes

- SUPDM56HW hardwire PDU
- Mounting Hardware
- Owner's Manual

## Specifications

OVERVIEW	
Model Type	PDU Modules
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	120/208, 120/240
Outlet Quantity / Type	Split-phase hardwire (4-wire)
Number of Outlets	0



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC
Input Connection Type	Split-phase hardwire (4-wire)
Voltage Compatibility (VAC)	100-140
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.75 x 12 x 10
Shipping Dimensions (hwd / cm)	14.6 x 30.5 x 25.4
Shipping Weight (lbs.)	4
Shipping Weight (kg)	1.8
Unit Dimensions (hwd / in.)	6 x 8.25 x 3.25
Unit Dimensions (hwd / cm)	15.24 x 21 x 8.3
Unit Weight (lbs.)	2.75
Unit Weight (kg)	1.24
Material of Construction	Steel
CERTIFICATIONS	
Certifications	Tested to UL1778 (USA), CSA (Canada), RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.