


NOTES:

- 1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
AND STANDARD APPLICATORS (RIGHT-LEFT FEED).
- 2 REELED WITH PAPER COVER.
- 3 SPLICE FREE CODE 115-10003.1
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



GENERAL TOLERANCES ± 0.3

4
OBSOLETE

	-	-	-
1	PRE-TINPLATED	PH.BRONZE	6-160913-8
1	PRE-TINPLATED	BRASS	6-160913-7
1	TINPLATED	PH.BRONZE	160913-4
3 1	UNPLATED	PH.BRONZE	160913-3
1	TINPLATED	BRASS	160913-2
1	UNPLATED	BRASS	160913-1

		NOTES			FINISH			MATERIAL	PARTNUMBER
E2	ECO-09-025699	KK	AEG	18DEC09	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED				
E1	4,4 was 4,1	J.L	J.L	7/JUL/2006	© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.				
E	ES00-0008-03	JL	JL	17JAN03	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION				
D	ES00-0065-01	JC	JL	19JUN01	Tyco Electronics Corporation Barcelona, Spain				
C	ES00-0043-01	JC	RS	2MAY01					
B	EH-1045-97	D.K.	R.V.	26 SEP 97					
A	EH-0168-94	DK	PB	21-06-94	NAME .250 SRS FASTIN-ON RECEPTACLE				
LTR.	REVISION RECORD	DR.	CHK.	DATE					
DR.: L.V.d.HEIJDEN		CHK.: A.BIJNEN		APP.: L.v.SOEST		DWG.No.		REV.LTR.	SHEET
DATE: 02-07-87		DATE: 10-08-87		DATE: 24-08-87		160913		E2	1 OF 1

WIRE RANGE :
>2,5-4,0 mm2
INSULATION RANGE :
3,3-4,5 DIA.