

Data Center Rack Cabinet Systems (DC100 Series)

[Home](#) > [Rack Index](#) > [Data Center Rack Cabinet Systems \(DC100\)](#)

DC100 Features:




Storage applications. This manufacturing principles

The DC100 series cabinets are offered in two capacities, 42U spaces and 24U spaces. A width of 24" allow cabinets to side or bay together matching standard placement, optimizing floor cable and cold access without conflict. Both cabinets have a total depth of 42" support deep server dimensions while providing additional space for cable management.

Please download our brochure for further information:

[PDF](#)



DC1004242 (420) Specific



universal-bql, zinc plated)

- ? Open bottle
- ? Removable
- 2 Premium h

- ? 4 x Leveling feet and recessed casters included
- ? Load capacity 2000 lbs
- ? Ships on standard pallet



- ? Top includes removable 14 gauge
- ? Overall height of 49.1

? Qty(25) black screws \$20 (1)- [1421ABK4](#) included



See cabinet system **accessories** below.



IN STOCK!

2000-01-000

(inches)					Weight lbs.
s	Units	Width	Depth	Height inches	




210

Instruction

4242	DC100 42U Locking Side Panel Kit (includes 2 x panels)
RAIL	EXTRA pair of squarehole, vertical mounting rails 42U high
RAIL	EXTRA pair of square-hole, vertical mounting rails 24U high
42	DC100 42U Air Dam Kit
24	DC100 24U Air Dam Kit
INGE	DC100 Right Hand Door Hinge
IP	DC100 Stabilizer / Anti-tip Bracket
	<p>Floor Bolt Down Kit (Required for Zone 4 compliance- see assembly instructions)</p>

DCT42

DCT24	DC Series 24U Vertical Cable Manager Tray
CGH01	Baying Hardware Kit (All Hammond Cabinets and Racks)



Mail Link To Our Catalog Department

Provide full mailing address here for your FREE CATALOG via snail mail.

[Home](#) | [Products](#) | [Where to purchase?](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)