


# Automotive MLCC

## General Specifications



### GENERAL DESCRIPTION

AVX Corporation has supported the Automotive Industry requirements for Multilayer Ceramic Capacitors consistently for more than 25 years. Products have been developed and tested specifically for automotive applications and all manufacturing facilities are QS9000 and VDA 6.4 approved.

AVX is using AECQ200 as the qualification vehicle for this transition. A detailed qualification package is available on request and contains results on a range of part numbers.

### HOW TO ORDER

| 0805                                                        | 5                                                                                                                     | A                                                  | 104                                                                                      | K                                                                                                                                                                                                                                                                                                           | 4                                       | T                                                                                                                | 2                                               | A                                      |
|-------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|----------------------------------------------------|------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------|------------------------------------------------------------------------------------------------------------------|-------------------------------------------------|----------------------------------------|
| <b>Size</b><br>0402<br>0603<br>0805<br>1206<br>1210<br>1812 | <b>Voltage</b><br>6.3V = 6<br>10V = Z<br>16V = Y<br>25V = 3<br>35V = D<br>50V = 5<br>100V = 1<br>200V = 2<br>500V = 7 | <b>Dielectric</b><br>NP0 = A<br>X7R = C<br>X8R = F | <b>Capacitance Code (in pF)</b><br>2 Sig. Digits +<br>Number of Zeros<br>e.g. 10 F = 106 | <b>Capacitance Tolerance</b><br>B = $\pm 0.1\text{pF}$ ( $<10\text{pF}$ )*<br>C = $\pm 0.25\text{pF}$ ( $<10\text{pF}$ )*<br>D = $\pm 0.5\text{pF}$ ( $<10\text{pF}$ )*<br>F = $\pm 1\%$ *<br>G = $\pm 2\%$ *<br>J = $\pm 5\%$ ( $\leq 1\mu\text{F}$ )<br>K = $\pm 10\%$<br>M = $\pm 20\%$<br><br>*NPO only | <b>Failure Rate</b><br><br>4=Automotive | <b>Terminations</b><br>T = Plated Ni and Sn<br>Z = FLEXITERM®**<br>U = Conductive Epo<br><br>**X7R      X8R only | <b>Packaging</b><br>2 = 7" Reel<br>4 = 13" Reel | <b>Special Code</b><br>A = Std.Product |

Contact factory for availability of Tolerance Options for Specific Part Numbers.

NOTE: Contact factory for non-specified capacitance values  
0402 case size available in T termination only.

### COMMERCIAL VS AUTOMOTIVE MLCC PROCESS COMPARISON


|                                                                | Commercial                                                             | Automotive                                                                                                |
|----------------------------------------------------------------|------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|
| <b>Administrative</b>                                          | Standard Part Numbers.<br>No restriction on who purchases these parts. | Specific Automotive Part Number. Used to control supply of product to Automotive customers.               |
| <b>Lot Qualification (Destructive Physical Analysis - DPA)</b> | As per EIA RS469                                                       | Increased sample plan stricter criteria.                                                                  |
| <b>Visual/Cosmetic Quality</b>                                 | Standard process and inspection                                        | 100% inspection                                                                                           |
| <b>Application Robustness</b>                                  | Standard sampling for accelerated wave solder on X7R dielectrics       | Increased sampling for accelerated wave solder on X7R and NP0 followed by lot by lot reliability testing. |

All Tests have Accept/Reject Criteria 0/1

Automotive MLCC  
NP0/X7R Dielectric

FLEXITERM FEATURES

- a) Bend Test  
The capacitor is soldered to the PC Board as shown:



Typical bend test results are shown below:

| Style | Conventional | Soft Term |
|-------|--------------|-----------|
| 0603  | >2mm         | >5        |
| 0805  | >2mm         | >5        |
| 1206  | >2mm         | >5        |

- a) Temperature Cycle testing  
FLEXITERM® has the ability to withstand at least 1000 cycles between -55°C and +125°C

# Automotive MLCC-NP0

## Capacitance Range



| SIZE      |      | 0402        |     | 0603        |     |      |      | 0805        |     |      |      |      | 1206        |     |      |      |      |      |
|-----------|------|-------------|-----|-------------|-----|------|------|-------------|-----|------|------|------|-------------|-----|------|------|------|------|
| Soldering |      | Reflow/Wave |     | Reflow/Wave |     |      |      | Reflow/Wave |     |      |      |      | Reflow/Wave |     |      |      |      |      |
| WVDC      |      | 25V         | 50V | 25V         | 50V | 100V | 200V | 25V         | 50V | 100V | 200V | 250V | 25V         | 50V | 100V | 200V | 250V | 500V |
| 0R5       | 0.5  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 1R0       | 1.0  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 1R2       | 1.2  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 1R5       | 1.5  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 1R8       | 1.8  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 2R2       | 2.2  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 2R7       | 2.7  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 3R3       | 3.3  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 3R9       | 3.9  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 4R7       | 4.7  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 5R6       | 5.6  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 6R8       | 6.8  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 8R2       | 8.2  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 100       | 10.0 | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 120       | 12   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 150       | 15   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 180       | 18   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 220       | 22   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 270       | 27   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 330       | 33   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 390       | 39   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 470       | 47   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    | J    | J    |
| 510       | 51   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 560       | 56   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 680       | 68   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 820       | 82   | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 101       | 100  | C           | C   | G           | G   | G    | G    | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 121       | 120  |             |     | G           | G   | G    |      | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 151       | 150  |             |     | G           | G   | G    |      | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 181       | 180  |             |     | G           | G   | G    |      | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 221       | 220  |             |     | G           | G   | G    |      | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 271       | 270  |             |     | G           | G   | G    |      | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 331       | 330  |             |     | G           | G   | G    |      | J           | J   | J    | N    | N    | J           | J   | J    | J    |      |      |
| 391       | 390  |             |     | G           | G   |      |      | J           | J   | J    |      |      | J           | J   | J    | J    |      |      |
| 471       | 470  |             |     | G           | G   |      |      | J           | J   | J    |      |      | J           | J   | J    | J    |      |      |
| 561       | 560  |             |     | G           | G   |      |      | J           | J   | J    |      |      | J           | J   | J    | J    |      |      |
| 681       | 680  |             |     | G           | G   |      |      | J           | J   | J    |      |      | J           | J   | J    | J    |      |      |
| 821       | 820  |             |     |             |     |      |      | J           | J   | J    |      |      | J           | J   | J    | J    |      |      |
| 102       | 1000 |             |     |             |     |      |      | J           | J   | J    |      |      | J           | J   | J    | J    |      |      |
| 122       | 1200 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 152       | 1500 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 182       | 1800 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 222       | 2200 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 272       | 2700 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 332       | 3300 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 392       | 3900 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 472       | 4700 |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| 103       | 10nF |             |     |             |     |      |      |             |     |      |      |      |             |     |      |      |      |      |
| WVDC      |      | 25V         | 50V | 25V         | 50V | 100V | 200V | 25V         | 50V | 100V | 200V | 250V | 25V         | 50V | 100V | 200V | 250V | 500V |
| Size      |      | 0402        |     | 0603        |     |      |      | 0805        |     |      |      |      | 1206        |     |      |      |      |      |

| Letter         | A               | C               | E               | G               | J               | K               | M               | N               | P               | Q               | X               | Y               | Z               |
|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| Max. Thickness | 0.33<br>(0.013) | 0.56<br>(0.022) | 0.71<br>(0.028) | 0.90<br>(0.035) | 0.94<br>(0.037) | 1.02<br>(0.040) | 1.27<br>(0.050) | 1.40<br>(0.055) | 1.52<br>(0.060) | 1.78<br>(0.070) | 2.29<br>(0.090) | 2.54<br>(0.100) | 2.79<br>(0.110) |
| PAPER          |                 |                 |                 |                 |                 | EMBOSSED        |                 |                 |                 |                 |                 |                 |                 |

Automotive MLCC - X7R

Capacitance Range



| Size         |            | 0402                          |     |     |     |     | 0603                           |     |      |      |      | 0805                          |     |     |      |      | 1206                         |     |     |     |      | 1210                         |      |      |     |     | 1812                           |      |      |      |      | 2220                           |     |     |      |      |      |   |   |
|--------------|------------|-------------------------------|-----|-----|-----|-----|--------------------------------|-----|------|------|------|-------------------------------|-----|-----|------|------|------------------------------|-----|-----|-----|------|------------------------------|------|------|-----|-----|--------------------------------|------|------|------|------|--------------------------------|-----|-----|------|------|------|---|---|
| Soldering    |            | Reflow/Wave                   |     |     |     |     | Reflow/Wave                    |     |      |      |      | Reflow/Wave                   |     |     |      |      | Reflow/Wave                  |     |     |     |      | Reflow Only                  |      |      |     |     | Reflow Only                    |      |      |      |      | Reflow Only                    |     |     |      |      |      |   |   |
| (L) Length   | mm (in.)   | 1 ± 0.1<br>(0.04 ± 0.004)     |     |     |     |     | 1.6 ± 0.15<br>(0.063 ± 0.006)  |     |      |      |      | 2.01 ± 0.2<br>(0.079 ± 0.008) |     |     |      |      | 3.2 ± 0.2<br>(0.126 ± 0.008) |     |     |     |      | 3.2 ± 0.2<br>(0.126 ± 0.008) |      |      |     |     | 4.5 ± 0.3<br>(0.177 ± 0.012)   |      |      |      |      | 5.7 ± 0.5<br>(0.224 ± 0.02)    |     |     |      |      |      |   |   |
| (W) Width    | mm (in.)   | 0.5 ± 0.1<br>(0.02 ± 0.004)   |     |     |     |     | 0.81 ± 0.15<br>(0.032 ± 0.006) |     |      |      |      | 1.25 ± 0.2<br>(0.049 ± 0.008) |     |     |      |      | 1.6 ± 0.2<br>(0.063 ± 0.008) |     |     |     |      | 2.5 ± 0.2<br>(0.098 ± 0.008) |      |      |     |     | 3.2 ± 0.2<br>(0.126 ± 0.008)   |      |      |      |      | 5 ± 0.4<br>(0.197 ± 0.016)     |     |     |      |      |      |   |   |
| (t) Terminal | mm (in.)   | 0.25 ± 0.15<br>(0.01 ± 0.006) |     |     |     |     | 0.35 ± 0.15<br>(0.014 ± 0.006) |     |      |      |      | 0.5 ± 0.25<br>(0.02 ± 0.01)   |     |     |      |      | 0.5 ± 0.25<br>(0.02 ± 0.01)  |     |     |     |      | 0.5 ± 0.25<br>(0.02 ± 0.01)  |      |      |     |     | 0.61 ± 0.36<br>(0.024 ± 0.014) |      |      |      |      | 0.64 ± 0.39<br>(0.025 ± 0.015) |     |     |      |      |      |   |   |
| WVDC         |            | 16V                           | 25V | 50V | 10V | 16V | 25V                            | 50V | 100V | 200V | 250V | 16V                           | 25V | 50V | 100V | 200V | 250V                         | 16V | 25V | 50V | 100V | 200V                         | 250V | 500V | 16V | 25V | 50V                            | 100V | 200V | 250V | 500V | 16V                            | 25V | 50V | 100V | 250V | 500V |   |   |
| 101          | 100        |                               |     |     |     |     |                                |     |      |      |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 221          | 220        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 271          | 270        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 331          | 330        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 391          | 390        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 471          | 470        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 561          | 560        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 681          | 680        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 821          | 820        | C                             | C   | C   | G   | G   | G                              | G   | G    | G    |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     |                                |      |      |      |      |                                |     |     |      |      |      |   |   |
| 102          | 1000       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 122          | 1220       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 152          | 1500       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 182          | 1800       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 222          | 2200       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 272          | 2700       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 332          | 3300       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 392          | 3900       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 472          | 4700       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 562          | 5600       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 682          | 6800       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 822          | 8200       | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 103          | Cap 0.01   | C                             | C   | C   | G   | G   | G                              | G   | G    | G    | G    | J                             | J   | J   | J    | J    | J                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 123          | (uF) 0.012 | C                             |     |     | G   | G   | G                              | G   | G    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 153          | 0.015      | C                             |     |     | G   | G   | G                              | G   | G    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 183          | 0.018      | C                             |     |     | G   | G   | G                              | G   | G    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 223          | 0.022      | C                             |     |     | G   | G   | G                              | G   | G    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 273          | 0.027      | C                             |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 333          | 0.033      | C                             |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | J    | J    | J   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 393          | 0.039      |                               |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | J                            | M    | M    | M   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 473          | 0.047      |                               |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    | N    | N                            | J   | J   | J   | J    | M                            | M    | M    | M   | K   | K                              | K    | K    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 563          | 0.056      |                               |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    |      |                              | J   | J   | J   | M    | M                            | M    | M    | M   | K   | K                              | K    | M    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 683          | 0.068      |                               |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    |      |                              | J   | J   | J   | M    | M                            | M    | M    | M   | K   | K                              | K    | M    | M    | Q    | K                              | K   |     |      |      |      |   |   |
| 823          | 0.082      |                               |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    |      |                              | J   | J   | J   | M    | M                            | M    | M    | M   | K   | K                              | K    | M    | Q    | K    | K                              |     |     |      |      |      |   |   |
| 104          | 0.1        |                               |     |     | G   | G   | G                              | G   | J    |      |      | J                             | J   | J   | N    |      |                              | J   | J   | J   | M    | P                            | P    | P    | P   | K   | K                              | K    | M    | Q    | K    | K                              |     |     |      |      |      | X |   |
| 124          | 0.12       |                               |     |     | G   | J   | J                              |     |      |      |      | J                             | J   | J   | N    | N    |                              | J   | J   | J   | M    | M                            | Q    | Q    | Q   | K   | K                              | K    | P    | Q    | K    | K                              |     |     |      |      |      |   |   |
| 154          | 0.15       |                               |     |     | G   | J   | J                              |     |      |      |      | M                             | N   | N   | N    | N    |                              | J   | J   | M   | M    | Q                            | Q    | Q    | Q   | K   | K                              | K    | P    | Q    | K    | K                              |     |     |      |      |      |   |   |
| 224          | 0.22       |                               |     |     | G   | J   | J                              | J   |      |      |      | M                             | N   | N   | N    | N    |                              | J   | M   | M   | Q    | Q                            | Q    | Q    | Q   | M   | M                              | M    | P    | Q    | K    | K                              |     |     |      |      |      |   |   |
| 334          | 0.33       |                               |     |     |     |     |                                |     |      |      |      | N                             | N   | N   | N    | N    |                              | J   | M   | P   | Q    |                              |      |      |     | P   | P                              | P    | Q    | Z    | Z    | X                              | X   |     |      |      |      |   |   |
| 474          | 0.47       |                               |     |     |     |     |                                |     |      |      |      | N                             | N   | N   | N    | N    |                              | M   | M   | P   | Q    |                              |      |      |     | P   | P                              | P    | Q    |      |      | X                              | X   |     |      |      |      |   |   |
| 684          | 0.68       |                               |     |     |     |     |                                |     |      |      |      | N                             | N   | N   | N    | N    |                              | M   | Q   | Q   | Q    |                              |      |      |     | P   | P                              | Q    | X    |      |      | X                              | X   |     |      |      |      |   |   |
| 105          | 1          |                               |     |     |     |     |                                |     |      |      |      | N                             | N   | N   | N    | N    |                              | M   | Q   | Q   | Q    | Q                            |      |      |     | P   | Q                              | Q    | Z    |      |      | X                              | X   |     |      | Z    | Z    | X | X |
| 155          | 1.5        |                               |     |     |     |     |                                |     |      |      |      | N                             | N   |     |      |      |                              | Q   | Q   | Q   | Q    |                              |      |      |     | P   | Q                              | Z    | Z    |      |      | X                              | X   |     |      | Z    | Z    | Z | Z |
| 225          | 2.2        |                               |     |     |     |     |                                |     |      |      |      | N                             | N   |     |      |      |                              | Q   | Q   | Q   | Q    |                              |      |      |     | Z   | Z                              | Z    | Z    |      |      | Z                              | Z   |     |      | Z    | Z    |   |   |
| 335          | 3.3        |                               |     |     |     |     |                                |     |      |      |      |                               |     |     |      |      |                              | Q   | Q   | Q   |      |                              |      |      |     | X   | Z                              | Z    | Z    |      |      | Z                              | Z   |     |      | Z    | Z    |   |   |
| 475          | 4.7        |                               |     |     |     |     |                                |     |      |      |      |                               |     |     |      |      |                              | Q   | Q   | Q   |      |                              |      |      |     | X   | Z                              | Z    | Z    |      |      | Z                              | Z   |     |      | Z    | Z    |   |   |
| 106          | 10         |                               |     |     |     |     |                                |     |      |      |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     | Z   | Z                              |      |      |      |      | Z                              | Z   |     |      | Z    | Z    |   |   |
| 226          | 22         |                               |     |     |     |     |                                |     |      |      |      |                               |     |     |      |      |                              |     |     |     |      |                              |      |      |     |     | Z                              |      |      |      |      |                                | Z   |     |      |      |      |   |   |
| WVDC         |            | 16V                           | 25V | 50V | 10V | 16V | 25V                            | 50V | 100V | 200V | 250V | 16V                           | 25V | 50V | 100V | 200V | 250V                         | 16V | 25V | 50V | 100V | 200V                         | 250V | 500V | 16V | 25V | 50V                            | 100V | 200V | 250V | 500V | 16V                            | 25V | 50V | 100V | 250V | 500V |   |   |
| Size         |            | 0402                          |     |     |     |     | 0603                           |     |      |      |      | 0805                          |     |     |      |      | 1206                         |     |     |     |      | 1210                         |      |      |     |     | 1812                           |      |      |      |      | 2220                           |     |     |      |      |      |   |   |

| Letter | A | C | E | G | J | K | M | N | P | Q | X | Y | Z |
|--------|---|---|---|---|---|---|---|---|---|---|---|---|---|
|--------|---|---|---|---|---|---|---|---|---|---|---|---|---|

# Automotive MLCC - X8R

## Capacitance Range



| SIZE      |      |       | 0603        |     |      | 0805        |     |      | 1206        |     |
|-----------|------|-------|-------------|-----|------|-------------|-----|------|-------------|-----|
| Soldering |      |       | Reflow/Wave |     |      | Reflow/Wave |     |      | Reflow/Wave |     |
| WVDC      | WVDC |       | 25V         | 50V | 100V | 25V         | 50V | 100V | 25V         | 50V |
| 472       | pF   | 4700  | G           | G   | G    | J           | J   | J    | J           | J   |
| 562       |      | 5600  | G           | G   | G    | J           | J   | J    | J           | J   |
| 682       |      | 6800  | G           | G   | G    | J           | J   | J    | J           | J   |
| 822       |      | 8200  | G           | G   | G    | J           | J   | J    | J           | J   |
| 103       | uF   | 0.01  | G           | G   | G    | J           | J   | J    | J           | J   |
| 123       |      | 0.012 | G           | G   |      | J           | J   | N    | J           | J   |
| 153       |      | 0.015 | G           | G   |      | J           | J   | N    | J           | J   |
| 183       |      | 0.018 | G           | G   |      | J           | J   | N    | J           | J   |
| 223       |      | 0.022 | G           | G   |      | J           | J   | N    | J           | J   |
| 273       |      | 0.027 | G           | G   |      | J           | J   |      | J           | J   |
| 333       |      | 0.033 | G           | G   |      | J           | J   |      | J           | J   |
| 393       |      | 0.039 | G           | G   |      | J           | J   |      | J           | J   |
| 473       |      | 0.047 | G           | G   |      | J           | J   |      | J           | J   |
| 563       |      | 0.056 | G           |     |      | N           | N   |      | M           | M   |
| 683       |      | 0.068 | G           |     |      | N           | N   |      | M           | M   |
| 823       |      | 0.082 |             |     |      | N           | N   |      | M           | M   |
| 104       |      | 0.1   |             |     |      | N           | N   |      | M           | M   |
| 124       |      | 0.12  |             |     |      | N           | N   |      | M           | M   |
| 154       |      | 0.15  |             |     |      | N           | N   |      | M           | M   |
| 184       |      | 0.18  |             |     |      | N           |     |      | M           | M   |
| 224       |      | 0.22  |             |     |      | N           |     |      | M           | M   |
| 274       |      | 0.27  |             |     |      |             |     |      | M           | M   |
| 334       |      | 0.33  |             |     |      |             |     |      | M           | M   |
| 394       |      | 0.39  |             |     |      |             |     |      | M           | M   |
| 474       |      | 0.47  |             |     |      |             |     |      | M           | Q   |
| 684       |      | 0.68  |             |     |      |             |     |      | Q           | Q   |
| 824       |      | 0.82  |             |     |      |             |     |      | Q           | Q   |
| 105       |      | 1     |             |     |      |             |     |      | Q           | Q   |
| WVDC      | WVDC |       | 25V         | 50V | 100V | 25V         | 50V | 100V | 25V         | 50V |
| SIZE      |      |       | 0603        |     |      | 0805        |     |      | 1206        |     |

| Letter         | A               | C               | E               | G               | J               | K               | M               | N               | P               | Q               | X               | Y               | Z               |
|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| Max. Thickness | 0.33<br>(0.013) | 0.56<br>(0.022) | 0.71<br>(0.028) | 0.90<br>(0.035) | 0.94<br>(0.037) | 1.02<br>(0.040) | 1.27<br>(0.050) | 1.40<br>(0.055) | 1.52<br>(0.060) | 1.78<br>(0.070) | 2.29<br>(0.090) | 2.54<br>(0.100) | 2.79<br>(0.110) |
| PAPER          |                 |                 |                 |                 |                 | EMBOSSED        |                 |                 |                 |                 |                 |                 |                 |