




Copyright FCI.

Product number
SEE TABLE, SHT 5



rev	ecn no	dr	date
A	S07-0103	LS	2007-04-05
B	S08-0251	LS	2008-07-31
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-


www.fciconnect.com			surface -  ASME Y14.5		tolerance std ASME Y14.5 -					
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	T. HOUTZ	2005-06-24	ANGULAR	LINEAR	0.X	±	size A4	Scale 5:2		
Eng	C. SHELLY	2005-06-24			0.XX	±				
Chr	C. H TAN	2008-07-31			0° ±°	0.XXX			±	
Appr	JOEY NG	2008-07-31	Product family AirMax VS					ECN *** Spec ref		
			title AirMax VS R/A HEADER ASSY PRESS-FIT, 72 POS, 14MM				dwg no 10052825		Rev. B	
catalog no			-				CUSTOMER		sheet 1 of 5	

REV F - 2008-04-17



Copyright FCI.

DESCRIPTION	DIM A	DIM B	DIM C
2-14MM MODULES PLACED END-TO-END	4.00	13.90 2X	14.00
1-12MM MODULE & 1-14MM MODULE PLACED END-TO-END	3.00	11.90 1X & 13.90 1X	13.00



DETAIL A

RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6 & 7




title	AirMax VS R/A HEADER ASSY PRESS-FIT, 72 POS, 14MM	dwg no	10052825	Rev.	B
catalog no	-	CUSTOMER	sheet 2 of 5		



Copyright FCI.

DESCRIPTION	DIM D	DIM E	DIM F
2-14MM MODULES PLACED END-TO-END	4.00	13.90 2X	14.00
1-12MM MODULE & 1-14MM MODULE PLACED END-TO-END	3.00	11.90 1X & 13.90 1X	13.00





RECOMMENDED PCB LAYOUT
FOR SINGLE ENDED APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6 & 7

	title	AirMax VS R/A HEADER ASSY		dwg no	10052825		Rev. B
		PRESS-FIT, 72 POS, 14MM					
	catalog no	-			CUSTOMER	sheet 3 of 5	



Copyright FCI.



PART NUMBER	PRESS-FIT TAIL PLATING TYPE	SHORT DETECT CONTACT
10052825-101	TIN/LEAD ALLOY OVER NICKEL	NO
10052825-101LF	TIN OVER NICKEL (LEAD FREE)	
10052825-111	TIN/LEAD ALLOY OVER NICKEL	YES (SEE NOTE 13)
10052825-111LF	TIN OVER NICKEL (LEAD FREE)	

NOTES:


1. CONNECTOR MATERIALS:
HOUSING & RETAINER: HIGH TEMP THERMOPLASTIC, NATURAL, UL94V-0
IMLA PLASTIC: HIGH TEMP THERMOPLASTIC, BLACK, UL94V-0
CONTACT: COPPER ALLOY

2. CONTACT PLATING:
SEPARABLE INTERFACE:
PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-239, INCLUDING TELCORDIA GR-1217-CORE (NOVEMBER 1995) CENTRAL OFFICE.
PRESS-FIT TAILS: SEE TABLE

3. PRODUCT SPECIFICATION: GS-12-239

4. APPLICATION SPECIFICATION: GS-20-035

5. PRODUCT MARKING, (PART NUMBER & LOT CODE), ON THIS SURFACE
6. REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES
7. POSITIONS F OF ODD NUMBERED COLUMNS AND POSITIONS G OF EVEN NUMBERED COLUMNS CORRESPOND TO EARLY MATE HEADER PINS
8. THERE IS NO GROUND BUSSING WITHIN THE CONNECTOR SYSTEM
9. REFER TO CUSTOMER DRAWING 10045979 FOR INFORMATION ON PCB HOLE DIAMETERS AND PLATING OPTIONS.



10. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
11. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
12. PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.
13. MATING PIN F4 IS SHORTER THAN ALL REMAINING SIGNAL PINS. NOMINAL MATING WIPE FOR PIN F4 IS 0.5MM LESS THAN ALL REMAINING SIGNAL PINS.
14. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

	title	AirMax VS R/A HEADER ASSY	dwg no	10052825	Rev.	B
	catalog no	-	CUSTOMER	sheet 5 of 5		