

NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
   X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
   350mA, 110V AC/DC
5. OPERATING FORCE: 425±100 CM/STANDARD
6. OPERATING TEMP: −30° to 85°C
7. ▲ CIRCUIT SP: 8 POSITIONS, 30° INDEX.
8. DIELECTRIC STRENGTH: 1000V RMS min.@Sea Level
9. ▲ TIMING: BBM (Non-Shorting) Break Before Make.
10. ▲ HARDWARE SUPPLIED ON SWITCH− SEE BELOW
    STOP RING, LOCKWASHER, & HEXNUT
11. ▲ DENOTES CRITICAL PARAMETER.



CONTACT CONFIGURATION
(SEE NOTE 10)



TERMINATION DETAIL
SCALE 2X

REV.	ECN No.	DESCRIPTION	DATE	CHKD
A	13083	RELEASED FOR PRODUCTION	4/24/03	AR

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE: KC18A10.001NLS

SCALE	DATE	DR	DWG	REV
1.5:1	4/24/03	AR	G530158	A