




PARAMETERS	SYMBOL	MAX.	TYP.	UNITS
POWER DISSIPATION	P_D	80		mW
Ave FORWARD CURRENT	I_{AF}	--		mA
PEAK FORWARD CURRENT	I_{PF}	100		mA
REVERSE VOLTAGE	V_R	5		V
FORWARD VOLTAGE	V_F	2.6	2	V
REVERSE CURRENT	I_R		100	μ A
EMISSION WAVELENGTH	λ_P		570	nm
LUMINOUS INTENSITY	I_v		30	mcd




SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
1-1a	OPEN



NOTES:

-



ORTHOGRAPHIC PROJECTION

FOR CLARITY ONLY

10. OPERATING TEMP, RANGE: -25°C to +85°C				
B	11666	REVISED & REDRAWN	9/20/01	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSMITTED				
TITLE				
R1966A BLK BLK E F GRN				
SCALE	DATE	DR	DWG	REV
1.5:1	9/20/01	CB	M301101	B