


## Features

- Diffused Junction
- Low Leakage
- Low Cost
- High Surge Current Capability
- Typical IR less than 200nA

## Mechanical Data

- Case: 13mm Bosch Type Press-Fit
- Terminals: Contact Areas Readily Solderable
- Polarity: Cathode to Case (Reverse Units Are Available Upon Request and Are Designated By A "R" Suffix, i.e. BD3520R or BD3524R)
- Polarity: Red Color Equals Standard, Black Color Equals Reverse Polarity
- Mounting Position: Any
- **Lead Free: For RoHS / Lead Free Version, Add "-LF" Suffix to Part Number, See Page 2**



13mm Bosch		
Dim	Min	Max
A	12.80	13.20
B	10.00	—
C	1.25	1.31
D	33.00	—
E	9.90	10.10

All Dimensions in mm

## Maximum Ratings and Electrical Characteristics $\text{@T}_A=25^\circ\text{C}$ unless otherwise specified

Single Phase, half wave, 60Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

Characteristic	Symbol	BD3520	BD3524	Unit
Peak Repetitive Reverse Voltage	$V_{RRM}$			
Working Peak Reverse Voltage	$V_{RWM}$			
DC Blocking Voltage	$V_R$			V
Average Rectified Output Current $\text{@T}_C = 150^\circ\text{C}$	$I_o$		35	A
Breakdown Voltage Min. $\text{@I}_R = 100\text{mA}$	$V_{BR}$	20		V
Breakdown Voltage Max. $\text{@I}_R = 100\text{mA}$		26	24 32	
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	$I_{FSM}$		400	A
Forward Voltage $\text{@I}_F = 35\text{A}$	$V_{FM}$		1.0	V
Peak Reverse Current At Rated DC Blocking Voltage $\text{@T}_A = 25^\circ\text{C}$	$I_{RM}$		200	nA
Typical Junction Capacitance (Note 1)	$C_j$		300	pF
Typical Thermal Resistance (Note 2)	$R_{\theta JC}$		1.2	$^\circ\text{C/W}$
Operating and Storage Temperature Range	$T_J, T_{STG}$		-65 to +175	$^\circ\text{C}$

Note: 1. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.  
2. Thermal Resistance: Junction to case, single side cooled.

## ORDERING INFORMATION

Product No.	Package Type	Shipping Quantity
BD3520	13mm Bosch Press-Fit	100 Units/Box
BD3524	13mm Bosch Press-Fit	100 Units/Box

1. Shipping quantity given is for minimum packing quantity only. For minimum order quantity, please consult the Sales Department.
2. **To order Lead Free version (with Lead Free finish), add “-LF” suffix to part number above. For example, BD3520-LF.**

Won-Top Electronics Co., Ltd (WTE) has checked all information carefully and believes it to be correct and accurate. However, WTE cannot assume any responsibility for inaccuracies. Furthermore, this information does not give the purchaser of semiconductor devices any license under patent rights to manufacturer. WTE reserves the right to change any or all information herein without further notice.

**WARNING:** DO NOT USE IN LIFE SUPPORT EQUIPMENT. WTE power semiconductor products are not authorized for use as critical components in life support devices or systems without the express written approval.

**Won-Top Electronics Co., Ltd.**  
No. 44 Yu Kang North 3rd Road, Chine Chen Dist., Kaohsiung, Taiwan  
**Phone:** 886-7-822-5408 or 886-7-822-5410  
**Fax:** 886-7-822-5417  
**Email:** sales@wontop.com  
**Internet:** <http://www.wontop.com>

*We power your everyday.*