

# HSMF-C15x

Bicolor Surface Mount Chip LEDs



## Reliability Data Sheet

HSMF-C153, HSMF-C155, HSMF-C156 and HSMF-C157

### Description

The following cumulative test results have been obtained from testing performed at Avago Technologies in accordance with the latest revisions of MIL-STD-883.

Avago Technologies tests parts at the absolute maximum rated conditions recommended for the device. The actual performance you obtain from Avago Technologies parts depends on the electrical and environmental characteristics of your application but will probably be better than the performance outlined in Table 1.

**Table 1. Life Tests**

### Demonstrated Performance

Colors	Stress Test Conditions	Total Device Hrs.	Units Tested	Units Failed	Point Typical Performance	
					MTBF	Failure Rate (% /1K Hours)
GaP HER/Yellow, AlInGaP Amber/Green, GaP Her/Green, GaP Yellow/Green, GaP Orange/Green	$T_A = 25^{\circ}\text{C}$ $I_F = 25\text{ mA}$	32,000	32	0	32,000	$\leq 3.125$
GaP HER/Yellow, AlInGaP Yellow/Green, GaP Her/Green, GaP Yellow/Green, GaP Orange/Green	$T_A = 55^{\circ}\text{C}$ $I_F = 5\text{ mA}$	88,000	88	0	88,000	$\leq 1.14$
GaP HER/Yellow, AlInGaP Yellow/Green, GaP Her/Green, GaP Yellow/Green, GaP Orange/Green	$T_A = -40^{\circ}\text{C}$ $I_F = 25\text{ mA}$	32,000	32	0	32,000	$\leq 3.125$

## Failure Rate Prediction

The failure rate of semiconductor devices is determined by the junction temperature of the device. The relationship between ambient temperature and actual junction temperature is given by the following:

$$T_J(^{\circ}\text{C}) = T_A(^{\circ}\text{C}) + \theta_{JA} P_{\text{AVG}}$$

where

$T_A$  = ambient temperature in  $^{\circ}\text{C}$

$\theta_{JA}$  = thermal resistance of junction-to-ambient in  $^{\circ}\text{C}/\text{watt}$

$P_{\text{AVG}}$  = average power dissipated in watts

The estimated MTBF and failure rate at temperatures lower than the actual stress temperature can be determined by using an Arrhenius model for temperature acceleration. Results of such calculations are shown in the table on the following page using an activation energy of 0.43 eV (reference MIL-HDBK-217).

**Table 2. Reliability Predictions ( $I_F = 25 \text{ mA DC}$ )**

### Demonstrated Performance

Ambient Temperature ( $^{\circ}\text{C}$ )	Junction Temperature ( $^{\circ}\text{C}$ )	Point Typical Performance in Time [1] (60% Confidence)		Performance in Time [2] (90% Confidence)	
		MTBF [1]	Failure Rate (%/1K Hours)	MTBF [2]	Failure Rate (%/1K Hours)
85	90	67,500	1.48	26,900	3.72
75	85	81,000	1.23	32,200	3.11
65	81	97,800	1.02	38,900	2.57
55	76	118,600	0.84	47,200	2.12
45	66	180,800	0.55	72,000	1.39
35	56	282,900	0.35	112,600	0.89
25	46	455,300	0.22	181,200	0.55

Notes:

[1] The point typical MTBF (which represents 60% confidence level) is the total device hours divided by the number of failures. In the case of zero failures, one failure is assumed for this calculation.

[2] The 90% Confidence MTBF represents the minimum level of reliability performance which is expected from 90% of all samples. This confidence interval is based on the statistics of the distribution of failures. The assumed distribution of failures is exponential. This particular distribution is commonly used in describing useful life failures. Refer to MIL-STD-690B for details on this methodology.

[3] A failure is any LED which does not emit light and maximum percent  $I_V$  degradation is  $>50\%$ .

### Example of Failure Rate Calculation

Assume a device operating 8 hours/day, 5 days/week. The utilization factor, given 168 hours/week is:

$$(8 \text{ hours/day}) \times (5 \text{ days/week}) / (168 \text{ hours/week}) = 0.25$$

The point failure rate per year (8760 hours) at  $25^{\circ}\text{C}$  ambient temperature is:

$$(0.22\% / 1\text{K hours}) \times (0.25) \times (8760 \text{ hours/year}) = 0.482\% \text{ per year}$$

Similarly, 90% confidence level failure rate per year at  $25^{\circ}\text{C}$ :

$$(0.55\% / 1\text{K hours}) \times (0.25) \times (8760 \text{ hours/year}) = 1.20\% \text{ per year}$$

**Table 3. Environmental Tests****(IR reflow solder processed at  $230 \pm 5^{\circ}\text{C}$  for 10 seconds)**

Test Name	Reference	Test Conditions	Units Tested	Units Failed
Temperature Cycle	MIL-STD-883 Method 1010	-40°C to 85°C, 15 min. dwell, 5 min. transfer, air to air storage		
		5 cycles	2300	0
		20 cycles	2300	0
		50 cycles	2300	0
		100 cycles	2800	2 open
		300 cycles	2298	0
Humidity Temperature Cycle		60°C, 90% RH, 10 mA		
		240 hours	32	0
		500 hours	32	0
		1000 hours	32	0
Temperature/Humidity Storage	JIS C 7021 Meth. B-11, cond. B	60°C, 90% RH, unbias		
		500 hours	50	0
High Temperature Storage	JIS C 7021 Meth. B-10, cond. C	85°C, unbias		
		1000 hours	50	0
Low Temperature Storage	JIS C 7021 Meth. B-12	-40°C, unbias		
		1000 hours	50	0
Solderability Test	JIS C 7021 Method A-2	230°C $\pm 5^{\circ}\text{C}$ , dwell time = 5 sec. $\pm 1$ sec.	50	0
Solder Resistance Test		250°C $\pm 15^{\circ}\text{C}$ , dwell time = 5 sec. $\pm 1$ sec.	50	0

**Table 4. Moisture Sensitivity Level Characterization****TEST MATRIX****(a) Visual Inspection Data**

Level	Reference	Precondition	Soak Time	3xIR	Floor Life	
					Time	Conditions
1	J-STD-020A	85°C/85% RH	168 hours	4 Minor lifted DA	1 year	- 30°C/85% RH
2a	J-STD-020A	85°C/60% RH	120 hours	0	4 weeks	- 30°C/60% RH
3	J-STD-020A	60°C/60% RH	40 hours	0	168 hours	- 30°C/60% RH
4	J-STD-020A	60°C/60% RH	20 hours	0	72 hours	- 30°C/60% RH

**(b) Electrical Test Data**

Level	Reference	3xIR	TMCL@ -40°C / 85°C		Floor Life	
			5x	20x	Time	Conditions
1	J-STD-020A	0	0	0	1 year	- 30°C/85% RH
2a	J-STD-020A	0	0	0	4 weeks	- 30°C/60% RH
3	J-STD-020A	0	0	0	168 hours	- 30°C/60% RH
4	J-STD-020A	0	0	0	72 hours	- 30°C/60% RH

**Conclusion:**

No functional failures were detected in all levels up to 20xTMCL. However, based on visual inspection data, minor lifted die-attach was found in lots that precondition with JEDEC Level 1 which potentially can affect long term reliability. Therefore, Chip LED was classified as a Level 2a product.

For product information and a complete list of distributors, please go to our web site: [www.avagotech.com](http://www.avagotech.com)

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies, Limited in the United States and other countries. Data subject to change. Copyright © 2006 Avago Technologies Pte. All rights reserved. Obsoletes 5989-1742EN  
AV01-0314EN - July 14, 2006

**Avago**  
TECHNOLOGIES