

Power Diodes

Schottky

1A Axial




Features:

- Low forward voltage drop
- High current capability
- High reliability
- High surge current capability

Mechanical Data:

Cases	: Moulded plastic DO-41
Lead	: Axial leads, solderable per MIL-STD-202, Method 208 guaranteed
Polarity	: Colour band denotes cathode end
High Temperature	: 260°C / 10 seconds / 0.375 inches, (9.5 mm) lead
Soldering Guaranteed	: lengths at 5 lbs., (2.3 kg) tension



Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	Symbol	1N5817	1N5818	1N5819	Unit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	40	V
Maximum RMS Voltage	V _{RMS}	14	21	28	
Maximum DC Blocking Voltage	V _{DC}	20	30	40	
Maximum Average Forward Rectified Current 0.375 Inches (9.5 mm) Lead Length at T _L = 90°C	I _(AV)	1			A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	25			
Maximum Instantaneous Forward Voltage at 1 A	V _F	0.45	0.55	0.6	V
Maximum Instantaneous Forward Voltage at 3 A		0.75	0.875	0.9	
Maximum DC Reverse Current at T _A = 25°C at Rated DC Blocking Voltage at T _A = 100°C	I _R	1 10			mA
Typical Thermal Resistance (Note 1)	R _{θJA} R _{θJC}	100 45			°C / W
Typical Junction Capacitance (Note 2)	C _J	55			pF
Operating Temperature Range	T _J	-65 to + 125			°C
Storage Temperature Range	T _{STG}				

Notes:

1. Mount on Cu-Pad Size 5 × 5 mm on PCB
2. Measured at 1 MHz and applied reverse voltage of 4 V dc

Schottky

Ratings and Characteristic Curves

Figure 1 Maximum Forward Current Derating Curve




Figure 2 Typical Junction Capacitance




Figure 3 Typical Forward Characteristics





Figure 4 Maximum Non-Repetitive Forward Surge Current



Specification Table

I_F (av) Maximum (A)	V_{RRM} Maximum (V)	V_F (V) at $I_F = 1$ A	I_{FSM} (A)	Length	Diameter	Package	Part Number
1	20	0.45	25	5.2	2.7	DO-41	1N5817
	30	0.55					1N5818
	40	0.87					1N5819

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.