

JTF Series



- High Power Density
- Wide 4:1 Input Range
- Operating Temperature -40°C to $+105^{\circ}\text{C}$
- Single & Dual Outputs
- Standard Remote On/Off
- 1600 VDC Isolation
- 3 Year Warranty

Specification

Input

Input Voltage Range	• 24 V (9-36 VDC) • 48 V (18-75 VDC)
Input Current	• See table
Input Filter	• Pi network
Input Reflected Ripple Current	• 20 mA pk-pk through 12 μH inductor and 47 μF capacitor, 5 Hz to 20 MHz
Input Surge	• 24 V models: 50 VDC for 100 ms (1 second for 12 W versions) • 48 V models: 100 VDC for 100 ms (1 second for 12 W versions)

Output

Output Voltage	• See table
Minimum Load	• No minimum load required
Initial Set Accuracy	• $\pm 1.0\%$ max for JTF15, $\pm 1.2\%$ for others
Start Up Delay	• 20 ms typical
Line Regulation	• $\pm 0.2\%$ max single, $\pm 0.5\%$ dual
Load Regulation	• $\pm 0.5\%$ max single, $\pm 1.0\%$ max dual
Cross Regulation	• $\pm 5\%$ on dual output models (see note 2)
Transient Response	• $< 3\%$ max deviation, recovery to within 1% in 250 μs for a 25% load change
Ripple & Noise	• 85 mV pk-pk, 20 MHz bandwidth for JTF08, JTF10 and JTF12, 60 mV pk-pk 20 MHz bandwidth for JTF15 (see note 3)
Overload Protection	• 150% of full load typical for JTF08 & JTF15, 170% of full load typical for JTF10 & JTF12
Overvoltage Protection	• 3.3 V models: 3.9 V typical • 5 V models: 6.2 V typical • 12 V models: 15 V typical • 15 V models: 18 V typical • ± 5 V models: ± 6.2 V typical • ± 12 V models: ± 15 V typical • ± 15 V models: ± 18 V typical
Short Circuit Protection	• Trip & restart (hiccup) with auto recovery
Maximum Capacitive Load	• See table
Temperature Coefficient	• $\pm 0.02/^{\circ}\text{C}$ max
Remote On/Off	• On: 3 to 12 VDC or open circuit • Off: < 1.2 VDC or short circuit pins 1, 2 & 3

General

Efficiency	• See tables
Isolation	• 1600 VDC Input to Output • 1600 VDC Input to Case • 1600 VDC Output to Case
Isolation Capacitance	• 2000 pF max for JTF15, 1500 pF max for others
Switching Frequency	• 330 kHz typical for JTF15, 270 kHz typical for others
Power Density	• JTF08: 20 W/in³, JTF10: 25 W/in³, JTF12: 30 W/in³, JTF15: 37.5 W/in³,
MTBF	• > 1 Mhrs to MIL-HDBK-217F at 25 $^{\circ}\text{C}$, GB

Environmental

Operating Temperature	• -40°C to $+105^{\circ}\text{C}$, derate from 100% load at $+60^{\circ}\text{C}$ to no load at $+105^{\circ}\text{C}$ for 10 W, 12 W and 15 W versions and from 100% load at 70°C to no load at 105°C for 8 W version
Case Temperature	• $+105^{\circ}\text{C}$ max
Storage Temperature	• -40°C to $+125^{\circ}\text{C}$
Humidity	• Up to 90%, non-condensing
Cooling	• Natural convection

EMC


Emissions	• EN55022 class A conducted with external components - see application note
ESD Immunity	• EN61000-4-2, level 3, Perf Criteria B
Radiated Immunity	• EN61000-4-3, 10 V/m Perf Criteria A
EFT/Burst	• EN61000-4-4, level 3 Perf Criteria B*
Surge	• EN61000-4-5, level 2 Perf Criteria B*
Conducted Immunity	• EN61000-4-6, 10 Vrms Perf Criteria A*
Magnetic Field	• EN61000-4-8, 1 A/m Perf Criteria A

* External input capacitor required, 330 $\mu\text{F}/100$ V.

Input Voltage	Output Voltage	Output Current	Input Current ⁽¹⁾		Max. Capacitive Load	Efficiency	Model Number
			No Load	Full Load			
9-36 V	3.3 V	2.0 A	10 mA	335 mA	1330 µF	83%	JTF0824S3V3
	5.0 V	1.5 A	10 mA	365 mA	1330 µF	86%	JTF0824S05
	12.0 V	0.665 A	15 mA	385 mA	288 µF	87%	JTF0824S12
	15.0 V	0.535 A	15 mA	385 mA	200 µF	87%	JTF0824S15
	±5.0 V	±0.8 A	10 mA	400 mA	±900 µF	84%	JTF0824D05
	±12.0 V	±0.335 A	15 mA	390 mA	±133 µF	86%	JTF0824D12
18-75 V	3.3 V	2.0 A	10 mA	170 mA	1330 µF	82%	JTF0848S3V3
	5.0 V	1.5 A	10 mA	185 mA	1330 µF	86%	JTF0848S05
	12.0 V	0.665 A	10 mA	195 mA	288 µF	87%	JTF0848S12
	15.0 V	0.535 A	10 mA	195 mA	200 µF	87%	JTF0848S15
	±5.0 V	±0.8 A	10 mA	200 mA	±900 µF	84%	JTF0848D05
	±12.0 V	±0.335 A	10 mA	195 mA	±133 µF	87%	JTF0848D12
9-36 V	3.3 V	2.7 A	15 mA	440 mA	1330 µF	85%	JTF1024S3V3
	5.0 V	2.0 A	15 mA	475 mA	1330 µF	87%	JTF1024S05
	12.0 V	0.833 A	15 mA	475 mA	288 µF	88%	JTF1024S12
	15.0 V	0.667 A	15 mA	480 mA	200 µF	88%	JTF1024S15
	±5.0 V	±1.0 A	15 mA	495 mA	±900 µF	85%	JTF1024D05
	±12.0 V	±0.417 A	15 mA	480 mA	±133 µF	87%	JTF1024D12
18-75 V	3.3 V	2.7 A	15 mA	225 mA	1330 µF	84%	JTF1048S3V3
	5.0 V	2.0 A	15 mA	240 mA	1330 µF	87%	JTF1048S05
	12.0 V	0.833 A	15 mA	240 mA	288 µF	87%	JTF1048S12
	15.0 V	0.667 A	15 mA	240 mA	200 µF	87%	JTF1048S15
	±5.0 V	±1.0 A	15 mA	250 mA	±900 µF	85%	JTF1048D05
	±12.0 V	±0.417 A	15 mA	245 mA	±133 µF	88%	JTF1048D12
9-36 V	3.3 V	3.5 A	15 mA	573 mA	2000 µF	87%	JTF1224S3V3
	5.0 V	2.4 A	15 mA	581 mA	2000 µF	89%	JTF1224S05
	12.0 V	1.0 A	15 mA	574 mA	430 µF	90%	JTF1224S12
	15.0 V	0.8 A	15 mA	574 mA	300 µF	90%	JTF1224S15
	±5.0 V	±1.2 A	15 mA	595 mA	±1250 µF	87%	JTF1224D05
	±12.0 V	±0.5 A	15 mA	574 mA	±200 µF	90%	JTF1224D12
18-75 V	3.3 V	3.5 A	15 mA	574 mA	±120 µF	90%	JTF1224D15
	5.0 V	2.4 A	15 mA	286 mA	2000 µF	87%	JTF1248S3V3
	12.0 V	1.0 A	15 mA	290 mA	2000 µF	89%	JTF1248S05
	15.0 V	0.8 A	15 mA	287 mA	430 µF	90%	JTF1248S12
	±5.0 V	±1.2 A	15 mA	297 mA	±1250 µF	87%	JTF1248D05
	±12.0 V	±0.5 A	15 mA	287 mA	±200 µF	90%	JTF1248D12
9-36 V	3.3 V	4.0 A	10 mA	647 mA	4700 µF	87%	JTF1524S3V3
	5.1 V	3.0 A	10 mA	732 mA	3300 µF	89%	JTF1524S05
	12.0 V	1.25 A	10 mA	710 mA	600 µF	90%	JTF1524S12
	15.0 V	1.0 A	10 mA	710 mA	400 µF	90%	JTF1524S15
	±5.0 V	±1.5 A	10 mA	744 mA	±1500 µF	86%	JTF1524D05
	±12.0 V	±0.625 A	10 mA	718 mA	±288 µF	89%	JTF1524D12
18-75 V	3.3 V	4.0 A	5 mA	327 mA	4700 µF	86%	JTF1548S3V3
	5.1 V	3.0 A	5 mA	370 mA	3300 µF	88%	JTF1548S05
	12.0 V	1.25 A	5 mA	355 mA	600 µF	90%	JTF1548S12
	15.0 V	1.0 A	5 mA	359 mA	400 µF	89%	JTF1548S15
	±5.0 V	±1.5 A	5 mA	372 mA	±1500 µF	86%	JTF1548D05
	±12.0 V	±0.625 A	5 mA	359 mA	±288 µF	89%	JTF1548D12



Notes

- Input current measured at nominal 24 V and 48 V input.
- When one output is set to 100% load & the other varies between 25% & 100% load.
- Measured with 1 µF ceramic capacitor across output rails.

Mechanical Details**Notes**

- All dimensions are in inches (mm)
- Weight: 0.04 lbs (18 g)
- Pin diameter: 0.02 ±0.002 (0.5 ±0.05)
- Pin pitch tolerance: ±0.014 (±0.35)
- Case tolerance: ±0.02 (±0.5)
- Package: 24 pin DIL nickel-coated copper.

Pin	Pin Connections	
	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin	-Vin
3	-Vin	-Vin
9	No Pin	Common
11	Not Connected	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin	+Vin
23	+Vin	+Vin

Application Notes**Derating Curve****Input Filter****Remote On/Off**

Standard ROF logic is positive
 Output On: 3 to 12 VDC or open circuit
 Output Off: <1.2 VDC or short circuit pins 1, 2 & 3