


3M™ Active Optical Cable (AOC) Assemblies for QSFP+ Applications
Visit <http://www.3Mconnectors.com>

REVISION RECORD		
REV.	ECR/ECN/ECO NUMBER	DATE
C	ECR/ECO-0048886	18/07/13
D	ECR/ECO-0052457	28/01/14



NOTES:

- SHELL MATERIAL: ZINC ALLOY
FINISHING: NICKEL PLATING
- UNLESS OTHERWISE NOTED, REFERENCES TO INDUSTRY SPECIFICATIONS ARE INTENDED TO INDICATE SUBSTANTIAL COMPLIANCE TO THE MATERIAL ELEMENTS OF THE SPECIFICATION. SUCH REFERENCES SHOULD NOT BE CONSTRUED AS A GUARANTEE OF COMPLIANCE TO ALL REQUIREMENTS IN A GIVEN SPECIFICATION.
- CABLE LENGTH TOLERANCE:

CABLE LENGTH	TOLERANCE
<10m	+40cm/-20cm
10m to 50m	+40cm/-30cm
>50m	+40cm/-50cm

3M PART NUMBERS

6A22-X04X1-XXX.0-0

STANDARD LENGTHS: 1 m INCREMENTS FROM 2m TO 30m,
35m, 40m, 45m, 50m, 60m, 70m, 80m, 90m, 100m

CABLE TYPE: 2 - ORANGE OM2+, PLENUM RATED THERMOPLASTIC
4 - ORANGE OM2+, LOW SMOKE ZERO HALOGEN RATED
THERMOPLASTIC (LSZH)

DATA RATE: A - QDR INFINIBAND / D - FDR INFINIBAND

PART NUMBER

DESCRIPTION

Example: 6A22-A0421-002.0-0 AOC, QSFP-QSFP, QDR INFINIBAND, 4CH, PLENUM, OM2+, 2m
6A22-D0441-003.0-0 AOC, QSFP-QSFP, FDR INFINIBAND, 4CH, LSZH, OM2+, 3m

UNIT: MM	DFTG	YUNLONG QIAO	DATE 18/07/13	3M APAC INNOVATION CENTRE	DIVISION	ESD	STATUS RELEASED
GEN. TOLERANCES	CHKD	YUNLONG QIAO	DATE 18/07/13		MODEL	_____	
LINEAR .0 = ± 0.20 .00 = ± 0.15 .000 = ± 0.05	APPVL	SAUJIT BANDHU	DATE 18/07/13	TITLE AOC, QSFP-QSFP, QDR/FDR, 4CH OPTICAL CABLE			
ANGLE ±1°	THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY TO 3M COMPANY. NO REPRODUCTION OR PUBLICATION OF THIS DOCUMENT, IN WHOLE OR IN PART, SHALL BE MADE WITHOUT AUTHORIZATION FROM 3M. ©3M 2014. ALL RIGHTS RESERVED.			SIZE A3	DRAWING NO.	78-5100-2442-1	REV D
PROJECTION 	INTERPRET PER ASME Y14.5M-1994						
	CRITICAL DIMENSION: ▲			SCALE : NTS		DET LIST ☐ YES ☐ NO	SHT 1 of 1
			6		7		8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[6A22-A0421-002.0-0](#) [6A22-A0421-004.0-0](#) [6A22-A0421-006.0-0](#) [6A22-A0421-008.0-0](#) [6A22-A0421-009.0-0](#) [6A22-A0421-011.0-0](#) [6A22-A0421-010.0-0](#) [6A22-A0421-012.0-0](#) [6A22-A0421-013.0-0](#) [6A22-A0421-014.0-0](#) [6A22-A0421-016.0-0](#) [6A22-A0421-017.0-0](#) [6A22-A0421-018.0-0](#) [6A22-A0421-019.0-0](#) [6A22-A0421-015.0-0](#) [6A22-A0421-020.0-0](#) [6A22-A0421-025.0-0](#) [6A22-A0421-003.0-0](#) [6A22-A0421-005.0-0](#) [6A22-A0421-030.0-0](#) [6A22-A0421-021.0-0](#) [6A22-A0421-022.0-1](#) [6A22-A0421-023.0-0](#) [6A22-A0421-024.0-0](#) [6A22-A0421-026.0-0](#) [6A22-A0421-027.0-0](#) [6A22-A0421-028.0-0](#) [6A22-A0421-029.0-0](#) [6A22-A0421-035.0-0](#) [6A22-A0421-040.0-0](#) [6A22-A0421-045.0-0](#) [6A22-A0421-050.0-0](#) [6A22-A0421-060.0-0](#) [6A22-A0421-070.0-0](#) [6A22-A0421-080.0-0](#) [6A22-A0421-090.0-0](#) [6A22-A0421-100.0-0](#) [6A22-A0441-002.0-0](#) [6A22-A0441-003.0-0](#) [6A22-A0441-004.0-0](#) [6A22-A0441-005.0-0](#) [6A22-A0441-006.0-0](#) [6A22-A0441-007.0-0](#) [6A22-A0441-008.0-0](#) [6A22-A0441-009.0-0](#) [6A22-A0441-010.0-0](#) [6A22-A0441-011.0-0](#) [6A22-A0441-012.0-0](#) [6A22-A0441-013.0-0](#) [6A22-A0441-014.0-0](#) [6A22-A0441-015.0-0](#) [6A22-A0441-016.0-0](#) [6A22-A0441-017.0-0](#) [6A22-A0441-018.0-0](#) [6A22-A0441-019.0-0](#) [6A22-A0441-020.0-0](#) [6A22-A0441-021.0-0](#) [6A22-A0441-022.0-0](#) [6A22-A0441-023.0-0](#) [6A22-A0441-024.0-0](#) [6A22-A0441-025.0-0](#) [6A22-A0441-026.0-0](#) [6A22-A0441-027.0-0](#) [6A22-A0441-028.0-0](#) [6A22-A0441-029.0-0](#) [6A22-A0441-030.0-0](#) [6A22-A0441-035.0-0](#) [6A22-A0441-040.0-0](#) [6A22-A0441-045.0-0](#) [6A22-A0441-050.0-0](#) [6A22-A0441-060.0-0](#) [6A22-A0441-070.0-0](#) [6A22-A0441-080.0-0](#) [6A22-A0441-090.0-0](#) [6A22-A0441-100.0-0](#)