

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.




LIGITEK

SUPER BRIGHT ROUND TYPE LED LAMPS


LVX3331

SERIES

Package Dimension



Directivity Radiation



Note: 1. All dimension are in millimeter tolerance is $\pm 0.25\text{mm}$ unless otherwise noted
 2. Specifications are subject to change without notice

• Part Selection And Application Information (Ratings At 25°C Ambient)

PART NO	MATERIAL	COLOR		Peak wave length λ_{Pnm}	Dominant wave length λ_{Dnm}	Spectral halfwidth $\Delta\lambda_{nm}$	Forward voltage @20mA(V)		Luminous intensity @20mA(mcd)		Viewing angle 2 θ 1/2 (deg)
		Emitted	Lens				Min.	Max.	Min.	Typ.	
LSR3331	GaAlAs	Red	Red Transparent	660	---	20	1.5	2.4	300	550	20
LHR3331	GaAlAs	Red	Red Transparent	660	---	20	1.5	2.4	550	900	20
LUR3331	GaAlAs	Red	Red Transparent	660	---	20	1.5	2.4	1100	2200	20
LVG3331	GaP	Green	Green Transparent	565	---	20	1.7	2.6	300	450	20
LVY3331	AlGaInP	Yellow	Yellow Transparent	---	595	15	1.7	2.6	900	1500	20
LUY3331	AlGaInP	Yellow	Yellow Transparent	---	595	15	1.7	2.6	1500	2700	20
LHY3331	AlGaInP	Yellow	Yellow Transparent	---	595	15	1.7	2.6	1100	2200	20
LUG3331	AlGaInP	Green	Green Transparent	---	574	20	1.7	2.6	550	900	20

• Absolute Maximum Rating (Ta=25°C)

PARAMETER	RED			GREEN		YELLOW				ORANGE		UNIT	REMARK
	SR	HR	UR	VG	UG	HY	VY	UY					
Forward Current	30	30	40	30	30	30	30	50				mA	
Peak Forward Current Duty 1/10@10KHz	100	100	120	120	120	60	60	90				mA	
Power Dissipation	100		120	100		75		120				mW	
Reverse Current @5v	10			10		10						μ A	
Operating Temperature	-40℃ TO +85℃												
Storage Temperature	-40℃ TO +100℃												

Lead Soldering Temperature 260°C For 5 Seconds(2.0mm From Body)