





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
CM	00		A1	REVISED PER ECO-11-005027	11MAR11	RK
						APVD HMR




- 1 WIRE RANGE: 0.13–0.32mm² (22–26 AWG).
- 2 INSULATION RANGE: 1.20–1.75 DIA.
- 3 FINISH: 0.76µm MIN GOLD OVER 1.27µm MIN NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 4 FINISH: 2.54µm MIN TIN ON ALL SURFACES IN THIS AREA.



SECTION A-A




SECTION B-B



SECTION C-C

GOLD		PHOS. BRZ.	1586317-4
PRE-TIN		PHOS. BRZ.	1586317-3
GOLD		BRASS	1586317-2
PRE-TIN		BRASS	1586317-1
FINISH:		MATERIAL:	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER	14-OCT-2003	 TE Connectivity						
		CHK D. COLEY	14-OCT-2003							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL LOOSE PIECE, SOCKET VAL-U-LOK(TM)						
		APVD D. COLEY						PRODUCT SPEC		
		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH		WEIGHT		A2		00779	C=1586317	—
		CUSTOMER DRAWING				SCALE	10:1	SHEET	1 of 1	REV A1