

< ATTACHMENT 1>

Main Specifications of the New 7.0-Inch LCD Module

Part number:	NL8048BC19-02
Resolution:	800(H) x 480(V) pixels
Display area:	152.4(H) x 91.44(V) mm Diagonal screen size of 7.0-inches (18cm)
Drive system:	Amorphous silicon TFT active matrix
Display color:	16.77M colors / 262K colors
Pixel arrangement:	RGB vertical stripe
Pixel pitch:	0.1905(H) x 0.1905(V) mm
Luminance:	400 cd/m ² (typ.)
Contrast ratio:	1000:1 (typ.)
Viewing angle:	Vertical : Up 80 degrees, down 80 degrees Horizontal : Left 80 degrees, right 80 degrees (contrast ratio at over 10:1)
Response time:	18 ms (typ.) (TON + TOFF: from 10% to 90%)
Interface:	LVDS (RGB 8 bits each / 6 bits each)
Power supply voltage:	3.3 V
Power consumption:	3.4 W (typ.)
Operating temperature:	-20 degrees C to + 70 degrees C
Storage temperature:	-30 degrees C to + 80 degrees C
Polarizer surface:	Clear
Module size:	170.0 (typ.) x 111.0 (typ.) x 9.0 (max.) mm
Weight:	165 g (typ.)
Backlight	White LED
Inverter:	Unnecessary

Note:

Please note that the press release and other information in this file may be out of date on observation. Please refer to other parts of NEC LCD Technologies' website for more current information.

**NEC LCD Technologies Announces New 7.0-inch Wide-Format LCD Modules
Featuring White LED Backlight System**

< ATTACHMENT 2>

Main Specifications of the New 6.5-Inch LCD Module

Part number:	NL10276BC13-01
Resolution:	1024(H) x 768(V) pixels
Display area:	132.096(H) x 99.072(V) mm Diagonal screen size of 6.5-inches (17cm)
Drive system:	Amorphous silicon TFT active matrix
Display color:	16.77M colors / 262K colors
Pixel arrangement:	RGB vertical stripe
Pixel pitch:	0.129(H) x 0.129(V) mm
Luminance:	500 cd/m ² (typ.)
Contrast ratio:	500:1 (typ.)
Viewing angle:	Vertical : Up 80 degrees, down 60 degrees Horizontal : Left 80 degrees, right 80 degrees (contrast ratio at over 10:1)
Response time:	25 ms (typ.) (TON + TOFF: from 10% to 90%)
Interface:	LVDS (RGB 8 bits each / 6 bits each)
Power supply voltage:	3.3 V
Power consumption:	3.9 W (typ.)
Operating temperature:	-20 degrees C to + 70 degrees C
Storage temperature:	-30 degrees C to + 80 degrees C
Polarizer surface:	Clear
Module size:	153.0 (typ.) x 118.0 (typ.) x 9.5 (max.) mm
Weight:	170 g (typ.)
Backlight	White LED
Inverter:	Unnecessary

Note:

Please note that the press release and other information in this file may be out of date on observation. Please refer to other parts of NEC LCD Technologies' website for more current information.